

1		2		3		4		5		6		7		8																																																																																																																																							
								REV. B	ECN NO. E3-810047	DATE 2007/12/24	SGN Jessie	DESCRIPTION Modify the Note And Change Part																																																																																																																																									
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTM. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTM.																																																																																																																																																					
Note: * $\varnothing$ Important Dimension. * Waterproof Rate: IP68 * Housing: Black, PU * Contact: Copper Alloy, Gold Plated * Wire: UL1007 24AWG * Ring: Green, Viton * Nut: Zinc, Nicked Plated																																																																																																																																																					
<table><tr><td>8</td><td>Orange 橘</td><td>8</td><td>8</td></tr><tr><td>7</td><td>Yellow 黄</td><td>7</td><td>7</td></tr><tr><td>6</td><td>Gray 灰</td><td>6</td><td>6</td></tr><tr><td>5</td><td>Red 红</td><td>5</td><td>5</td></tr><tr><td>4</td><td>Green 绿</td><td>4</td><td>4</td></tr><tr><td>3</td><td>Blue 蓝</td><td>3</td><td>3</td></tr><tr><td>2</td><td>White 白</td><td>2</td><td>2</td></tr><tr><td>1</td><td>Black 黑</td><td>1</td><td>1</td></tr><tr><td colspan="4">Conn.1 Wire Color Conn.2 Conn.3</td></tr></table>															8	Orange 橘	8	8	7	Yellow 黄	7	7	6	Gray 灰	6	6	5	Red 红	5	5	4	Green 绿	4	4	3	Blue 蓝	3	3	2	White 白	2	2	1	Black 黑	1	1	Conn.1 Wire Color Conn.2 Conn.3																																																																																																						
8	Orange 橘	8	8																																																																																																																																																		
7	Yellow 黄	7	7																																																																																																																																																		
6	Gray 灰	6	6																																																																																																																																																		
5	Red 红	5	5																																																																																																																																																		
4	Green 绿	4	4																																																																																																																																																		
3	Blue 蓝	3	3																																																																																																																																																		
2	White 白	2	2																																																																																																																																																		
1	Black 黑	1	1																																																																																																																																																		
Conn.1 Wire Color Conn.2 Conn.3																																																																																																																																																					
Pin Out																																																																																																																																																					
<table><tr><td>UNIT: mm</td><td></td><td colspan="13">TITLE M12 8Pin Adaptor</td></tr><tr><td>TOLERANCE</td><td>± 0.25</td><td colspan="13">ITEM NO SS-080808-FMM-YS001</td></tr><tr><td>.X</td><td>± 0.1</td><td colspan="13">DWG NO SS-080808-FMM-YS001</td></tr><tr><td>.XX</td><td>± 0.05</td><td colspan="13">CUSTOMER ALTW</td></tr><tr><td>ANGLES</td><td>$\pm 1^\circ$</td><td colspan="13">DRAWN BY Jessie</td></tr><tr><td colspan="2"></td><td colspan="13">CHECKED BY Cloud</td></tr><tr><td colspan="2"></td><td colspan="13">APPROVED BY Luke</td></tr><tr><td colspan="2"></td><td colspan="13">DATE 2007/12/24</td></tr><tr><td colspan="2"></td><td colspan="13">DATE 2007/12/24</td></tr></table>															UNIT: mm		TITLE M12 8Pin Adaptor													TOLERANCE	± 0.25	ITEM NO SS-080808-FMM-YS001													.X	± 0.1	DWG NO SS-080808-FMM-YS001													.XX	± 0.05	CUSTOMER ALTW													ANGLES	$\pm 1^\circ$	DRAWN BY Jessie															CHECKED BY Cloud															APPROVED BY Luke															DATE 2007/12/24															DATE 2007/12/24												
UNIT: mm		TITLE M12 8Pin Adaptor																																																																																																																																																			
TOLERANCE	± 0.25	ITEM NO SS-080808-FMM-YS001																																																																																																																																																			
.X	± 0.1	DWG NO SS-080808-FMM-YS001																																																																																																																																																			
.XX	± 0.05	CUSTOMER ALTW																																																																																																																																																			
ANGLES	$\pm 1^\circ$	DRAWN BY Jessie																																																																																																																																																			
		CHECKED BY Cloud																																																																																																																																																			
		APPROVED BY Luke																																																																																																																																																			
		DATE 2007/12/24																																																																																																																																																			
		DATE 2007/12/24																																																																																																																																																			
Rev. B Size A4 Inspection Item																																																																																																																																																					
Scale: Free Sheet 1 of 1																																																																																																																																																					
Company: 安費諾亮泰企業股份有限公司																																																																																																																																																					