

7BB-35-3L0

Note: This datasheet may be out of date.

Please download the latest datasheet of 7BB-35-3L0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=7BB-35-3L0










Appearance & Shape





Features

- 1. Clear sound
- 2. Ultra thin and lightweight
- 3. No contacts: therefore, no noise and highly reliable
- 4. Low power consumption for voltage type



Applications

| Other Usage | Consumer/Industrial |
|-------------|---------------------|
|-------------|---------------------|



Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| - | Bulk | 400 |

1 of 2

Attention

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





7BB-35-3L0

Note: This datasheet may be out of date.

Please download the latest datasheet of 7BB-35-3L0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=7BB-35-3L0



Specifications

| Resonance Frequency | 2.8kHz |
|--------------------------------------|----------------|
| Resonant Frequency Torelance | ±0.5kHz |
| Resonant Impedance (R1) | 200Ω |
| Capacitance | 30nF |
| Capacitance Tolerance | ±30% |
| Measurement Condition of Capacitance | [1kHz] |
| Operating Temperature Range | -20°C to 70°C |
| Storage Temperature Range | -30°C to 80°C |
| Shape | With lead wire |
| Plate Size | 35mm |
| Element Size | 25mm |
| Plate Material | Brass |
| Specification of Lead Wire | AWG32 |
| Lead Length | 50mm |
| Drive Type | External Drive |
| EIAJ Part Number | PD-SU2-C35-28 |
| Mass | 3356mg |

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

