

HC-B24-SP-CBK - Profile gasket



1411482

<https://www.phoenixcontact.com/us/products/1411482>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile gasket for HEAVYCON EVO supporting base element type B24, conductive



Commercial data

Item number	1411482
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF66
Product key	BF7APZ
Catalog page	Page 662 (C-2-2017)
GTIN	4046356932820
Weight per piece (including packing)	4.12 g
Weight per piece (excluding packing)	3.92 g
Customs tariff number	40169300
Country of origin	CN

HC-B24-SP-CBK - Profile gasket



1411482


<https://www.phoenixcontact.com/us/products/1411482>

Technical data

Product properties

Product type	Seal
Application	for base housing

Dimensions

Dimensional drawing	
Width	43.8 mm
Height	3800 mm
Length	120 mm

Material specifications

Material	NBR, conductive
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mounting

Assembly note	The replacement seal should be bonded with Loctite 454 adhesive. For HC-EVO-B24...AL housing and HC-STA-B24...AL
---------------	---


HC-B24-SP-CBK - Profile gasket

1411482

<https://www.phoenixcontact.com/us/products/1411482>



Drawings



Dimensional drawing

HC-B24-SP-CBK - Profile gasket



1411482

<https://www.phoenixcontact.com/us/products/1411482>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411482>



EAC

Approval ID: RU C-DE.AI30.B.01102

HC-B24-SP-CBK - Profile gasket



1411482

<https://www.phoenixcontact.com/us/products/1411482>

Classifications

ECLASS

ECLASS-11.0	23071590
ECLASS-12.0	23071590
ECLASS-13.0	23071590

ETIM

ETIM 9.0	EC002498
----------	----------

UNSPSC

UNSPSC 21.0	31401600
-------------	----------

HC-B24-SP-CBK - Profile gasket



1411482

<https://www.phoenixcontact.com/us/products/1411482>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com