

HC-STA-B24-DC-PL - Protective cover



1421103

<https://www.phoenixcontact.com/us/products/1421103>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover, design: B24

Commercial data

Item number	1421103
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	BF66
Product key	BF7AZC
Catalog page	Page 655 (C-2-2019)
GTIN	4055626251837
Weight per piece (including packing)	12 g
Weight per piece (excluding packing)	10.5 g
Customs tariff number	85389099
Country of origin	CN

HC-STA-B24-DC-PL - Protective cover



1421103


<https://www.phoenixcontact.com/us/products/1421103>

Technical data

Product properties

Product type	Protective cover
Housing type	Protective cover
Type	B24
Seal present	no

Dimensions

Dimensional drawing	
Width	46.4 mm
Height	22.1 mm
Length	123.2 mm

Material specifications

Color	transparent
Material Protective cover	PA
Flammability rating according to UL 94	HB

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 20 °C

HC-STA-B24-DC-PL - Protective cover


1421103

<https://www.phoenixcontact.com/us/products/1421103>



Drawings

Dimensional drawing



Dimensional drawing

HC-STA-B24-DC-PL - Protective cover

1421103

<https://www.phoenixcontact.com/us/products/1421103>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1421103>

DNV

Approval ID: TAE000037S

HC-STA-B24-DC-PL - Protective cover



1421103

<https://www.phoenixcontact.com/us/products/1421103>

Classifications

ECLASS

ECLASS-11.0	27440208
ECLASS-12.0	27440208
ECLASS-13.0	27440208

ETIM

ETIM 9.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-STA-B24-DC-PL - Protective cover



1421103

<https://www.phoenixcontact.com/us/products/1421103>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com