

SKS 8-D - Shield connection terminal block



3240213

<https://www.phoenixcontact.com/us/products/3240213>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection terminal block, for direct shield on conductive mounting panels

Your advantages

- As components, it is not possible to certify shield connections in accordance with the requirements of the directive and standards for electrical equipment in potentially explosive areas. As such, shield connection clamps can be used in the Ex area even without an appropriate approval or marking.
- Three different mounting types supported: on NS 35 DIN rails, on busbars, or directly on conductive mounting panels

Commercial data

Item number	3240213
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE75
Product key	BE7521
Catalog page	Page 569 (C-3-2019)
GTIN	4046356458665
Weight per piece (including packing)	11.2 g
Weight per piece (excluding packing)	11 g
Customs tariff number	85369010
Country of origin	DE

SKS 8-D - Shield connection terminal block



3240213

<https://www.phoenixcontact.com/us/products/3240213>

Technical data

Product properties

Product type	Shield connection clamp
Pitch	12.4 mm
Number of connections	1
Number of rows	1


Electrical properties

Maximum power dissipation for nominal condition	1.31 W
---	--------

Connection data

Screw thread	M4
Conductor cross section rigid	3 mm ² ... 8 mm ²
Cross section AWG	12 ... 10 (converted acc. to IEC)
Conductor cross section flexible	3 mm ² ... 8 mm ²
Conductor cross section, flexible [AWG]	12 ... 10 (converted acc. to IEC)

Dimensions

Dimensional drawing	
Width	12.4 mm
Height	18 mm
Depth	34.9 mm
Pitch	12.4 mm

Material specifications

Color	silver-colored
Material	Steel

Cable/line

External cable diameter	3 mm ... 8 mm
-------------------------	---------------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mounting

Mounting type	direct screw connection
---------------	-------------------------

SKS 8-D - Shield connection terminal block


3240213

<https://www.phoenixcontact.com/us/products/3240213>



Drawings

Dimensional drawing



SKS 8-D - Shield connection terminal block



3240213

<https://www.phoenixcontact.com/us/products/3240213>

Classifications

ECLASS

ECLASS-11.0	27141150
ECLASS-12.0	27141150
ECLASS-13.0	27250309

ETIM

ETIM 9.0	EC002020
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SKS 8-D - Shield connection terminal block



3240213

<https://www.phoenixcontact.com/us/products/3240213>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com