

BES 6 - Component connector

2802549

<https://www.phoenixcontact.com/us/products/2802549>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component connector, pitch: 6 mm, number of positions: 1, color: gray, mounting type: Plug-in mounting

Your advantages

- Is supplied as a set with two plug sockets

Commercial data

Item number	2802549
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BE19
Product key	BE1Z3X
Catalog page	Page 510 (C-1-2019)
GTIN	4017918074463
Weight per piece (including packing)	7.24 g
Weight per piece (excluding packing)	7.2 g
Customs tariff number	85366990
Country of origin	PL

BES 6 - Component connector

2802549

<https://www.phoenixcontact.com/us/products/2802549>



Technical data


Product properties

Product type	Component plug terminal block
Number of positions	1
Pitch	6 mm

Connection data

Tightening torque	0.5 ... 0.6 Nm
-------------------	----------------

Dimensions

Dimensional drawing	
Pitch	6 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V2
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Plug-in mounting
---------------	------------------

BES 6 - Component connector


2802549

<https://www.phoenixcontact.com/us/products/2802549>



Drawings

Circuit diagram




BES 6 - Component connector

2802549

<https://www.phoenixcontact.com/us/products/2802549>



Dimensional drawing



BES 6 - Component connector

2802549

<https://www.phoenixcontact.com/us/products/2802549>



Classifications

ECLASS

ECLASS-11.0	27141149
ECLASS-12.0	27141149
ECLASS-13.0	27250305

ETIM

ETIM 9.0	EC002018
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

BES 6 - Component connector

2802549

<https://www.phoenixcontact.com/us/products/2802549>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com