




Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Marking Accessories



Marking Product Type: **Label Holder**
Primary Product Color: **Dark Gray**
Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**
UL Flammability Rating: **UL 94V-0**
EU RoHS Compliance: **Compliant**

Features

Dimensions

Product Width	19.5 mm[.768 in]
Product Depth	29.5 mm
Product Length	35.65 mm[1.4 in]
Product Height	37.25 mm[.7 in]

Usage Conditions

Installation Temperature Range	-5 – 40 °C[23 – 104 °F]
Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Body Features

Product Weight	1.1 g[.038 oz]
Primary Product Material	Polyamide
Primary Product Color	Dark Gray

Product Type Features

Marking Product Type	Label Holder
----------------------	--------------

Industry Standards



UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1SNS470000Z0210
JBox Motor Spring



TE Part # 1SNK900634R0000
MCLH-R1-YL



TE Part # 1SNK900002R0000
BAZ1



TE Part # 1SNS470000Z0208
JBox 12PNT Spring



TE Part # 1SNA178430R0500
[CARTE 54 RCPEB](#)

TE Part # 1SNA235155R2600
[PIB2-TT](#)

TE Part # 1SNK900102R0000
[BAZH1](#)

TE Part # 1SNS470000Z0206
[JBox 6PNT Spring](#)

TE Part # 1SNS470000Z0209
[JBox 12PNT Screw](#)

TE Part # 1SNS470000Z0207
[JBox 6PNT Screw](#)

TE Part # 1SNA178431R2200
[EPR1](#)

TE Part # 1SNK900631R0000
[MCLH-R1](#)

TE Part # 1SNS470000Z0211
[JBox Motor Screw](#)

TE Part # 1SNK900001R0000
[BAM4](#)

Also in the Series | [ENTRELEC HTP600](#)

[Printer Accessories](#)(13)


[Printer Ribbons](#)(4)

[Printers](#)(1)

[Terminal Block & Strip Insulating Accessories](#)(3)

[Terminal Block & Strip Marking Accessories](#)(113)

Customers Also Bought



Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1SNK900607R0000_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900607R0000_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1SNK900607R0000_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

- LH-R1

English

SNK SERIES TERMINAL BLOCKS

English



[ENTRELEC Terminal Blocks Catalogue \(RUS\)](#)

[ENTRELEC Terminal Block - Master Catalog](#)

[ENTRELEC Terminal Block - Master Catalog](#)

English