

1424337

https://www.phoenixcontact.com/us/products/1424337

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.





Commercial data

Item number	1424337
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF60
Product key	BF7AHB
Catalog page	Page 684 (C-2-2019)
GTIN	4055626370750
Weight per piece (including packing)	51.8 g
Weight per piece (excluding packing)	51.6 g
Customs tariff number	85389099
Country of origin	CN



1424337

https://www.phoenixcontact.com/us/products/1424337

Technical data


Notes

General	for B24, BB48, DD108, HV10 contact inserts and B24 module frame
Notes on safety	Protection against electric shock must be ensured by the user. The continuity of the PE connection must be verified and satisfied by the user. The PE connection must be implemented equilaterally.

Product properties

Product type	DIN rail mounting frame
Housing type	DIN rail mounting frame
Series	HC-CIF-PL
Туре	B24
Protective cover	no
Pg screw connection	none

Dimensions



Material specifications

Material	PC
Flammability rating according to UL 94	V0

Mechanical properties

Mechanical data	
Locking type	Clip

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C 125 °C

Mounting



1424337

https://www.phoenixcontact.com/us/products/1424337

Assembly note	To ensure correct use, installation in an IP-protected space is required
---------------	--




1424337

https://www.phoenixcontact.com/us/products/1424337

Drawings

Dimensional drawing



Dimensional drawing



1424337

https://www.phoenixcontact.com/us/products/1424337

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1424337



cUL Recognized Approval ID: E118976



UL RecognizedApproval ID: E118976

cULus Recognized



1424337

https://www.phoenixcontact.com/us/products/1424337

Classifications

ECLASS

	ECLASS-11.0	27440210
	ECLASS-12.0	27440210
	ECLASS-13.0	27440210
ETIM		
	ETIM 9.0	EC002310
UN	NSPSC	
	UNSPSC 21.0	39121400



1424337

https://www.phoenixcontact.com/us/products/1424337

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 @ - all rights reserved https://www.phoenixcontact.com

Phoenix Contact USA 586 Fulling Mill Road Middletown, PA 17057, United States (+717) 944-1300 info@phoenixcon.com