



Pushing Performance
Since 1945

Han 10B-AK-LB-Dichtung



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 30 010 5432 |
| Specification | Han 10B-AK-LB-Dichtung |
| HARTING eCatalogue | https://b2b.harting.com/09300105432 |

Identification

| | |
|------------------------------|------------------|
| Category | Accessories |
| Series of hoods/housings | Han® B |
| Type of accessory | Protection cover |
| Description of the accessory | for hoods |
| | Metal |
| | With fixing cord |

Version

| | |
|----------------|----------------------|
| Size | 10 B |
| Locking type | Single locking lever |
| Han-Easy Lock® | Yes |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 |
| | 4X |
| | 12 |

Material properties

| | |
|--------------------|----------------------|
| Material (seal) | NBR |
| Material (locking) | Polycarbonate (PC) |
| | Stainless steel |
| Colour (locking) | RAL 7037 (dust grey) |



Pushing Performance
Since 1945

Material properties

| | |
|--|---|
| Material flammability class acc. to UL 94 (locking levers) | V-0 |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate |
| ECHA SCIP number | 60b1a572-bb3f-476f-9307-b7d1688bd90c |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Lead |
| | Nickel |
| | Naphthalene |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R22 (HL 1-3) |
| | R23 (HL 1-3) |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 76 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140045378 |
| ETIM | EC002314 |
| eCl@ss | 27440208 Cap for industrial connectors |