

# AB/NS - Support bracket



1201141

<https://www.phoenixcontact.com/us/products/1201141>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Support bracket, for insulated mounting of DIN rails in insulated systems, plastic, 21 mm high

## Your advantages

- The support can be used for fully insulated DIN rail support bracket

## Commercial data

Item number	1201141
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE07
Product key	BE7113
Catalog page	Page 545 (C-3-2019)
GTIN	4017918017248
Weight per piece (including packing)	17.27 g
Weight per piece (excluding packing)	17.16 g
Customs tariff number	39269097
Country of origin	DE

# AB/NS - Support bracket

1201141

<https://www.phoenixcontact.com/us/products/1201141>




## Technical data

### Product properties

Product type	Support bracket
--------------	-----------------

### Dimensions

Dimensional drawing	
Width	38 mm
Height	35 mm
Depth	21 mm
Length	35 mm
Diameter	7.2 mm

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V2
Coating	uncoated

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	Direct mounting
---------------	-----------------

# AB/NS - Support bracket


1201141

<https://www.phoenixcontact.com/us/products/1201141>



## Drawings

Dimensional drawing



# AB/NS - Support bracket

1201141

<https://www.phoenixcontact.com/us/products/1201141>



## Classifications

### ECLASS

ECLASS-11.0	27370419
ECLASS-12.0	27370419
ECLASS-13.0	27370419

### ETIM

ETIM 9.0	EC001024
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# AB/NS - Support bracket



1201141  
<https://www.phoenixcontact.com/us/products/1201141>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)