





REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	12NOV2021	C.C.	J.Y.
	A1	ECR-22-136442	11APR2022	S.T	Z.Z



-1 AS SHOWN

1. CODE VARIETY
2. APPLICATION TEMP. -40°C ~ 140°C




1-2399663-3	M	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 1-2399679-3	FOLLOW 2399663-1 PLUG TPA	- M	- PA66-GF	- AQUA RED	(40.94)	- 1	2-7 1
1-2399663-2	L	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 1-2399679-2	FOLLOW 2399663-1 PLUG TPA	- L	- PA66-GF	- AQUA BROWN	(40.94)	- 1	2-7 1
1-2399663-1	K	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 1-2399679-1	FOLLOW 2399663-1 PLUG TPA	- K	- PA66-GF	- AQUA GREEN	(40.94)	- 1	2-7 1
2399663-9	J	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-9	FOLLOW 2399663-1 PLUG TPA	- J	- PA66-GF	- ORANGE	(40.94)	- 1	2-7 1
2399663-8	H	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-8	FOLLOW 2399663-1 PLUG TPA	- H	- PA66-GF	- YELLOW	(40.94)	- 1	2-7 1
2399663-7	G	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-7	FOLLOW 2399663-1 PLUG TPA	- G	- PA66-GF	- RED	(40.94)	- 1	2-7 1
2399663-6	F	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-6	FOLLOW 2399663-1 PLUG TPA	- F	- PA66-GF	- BROWN	(40.94)	- 1	2-7 1
2399663-5	E	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-5	FOLLOW 2399663-1 PLUG TPA	- E	- PA66-GF	- GREEN	(40.94)	- 1	2-7 1
2399663-4	D	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-4	FOLLOW 2399663-1 PLUG TPA	- D	- PA66-GF	- PURPLE	(40.94)	- 1	2-7 1
2399663-3	C	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-3	FOLLOW 2399663-1 PLUG TPA	- C	- PA66-GF	- BLUE	(40.94)	- 1	2-7 1
2399663-2	B	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	- 2399679-2	FOLLOW 2399663-1 PLUG TPA	- B	- PA66-GF	- NATURE	(40.94)	- 1	2-7 1
2399663-1	A	PLUG ASSEMBLY HVP-HD1400 FINGER ACCESS	2399675-1	PLUG HOUSING	-	PA66-GF	ORNGE	(40.94)	1	7
			2399676-1	SHIELD	-	COPPER ALLOY	AG PLATED		1	6
			2395531-1	CPA - FINGER ACCESS	-	PA66-GF	RED		1	5
			2395532-1	CPA SPRING - FINGER ACCESS	-	STAINLESS STEEL	-		1	4
			2383848-1	HVIL	-	COPPER	AG PLATED		1	3
			2399677-1	PERIPHERAL SEAL	-	SILICONE	GREEN		1	2
TE ASSY NO.	CODE	DESCRIPTION	TE PART NO.	COMPONENT	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM
			2399679-1	PLUG TPA	A	PA66-GF	BLACK		1	1



FOR FINGER ACCESS


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.AO	12NOV2021	TE Connectivity	
DIMENSIONS: mm		CHK J.L.I	12NOV2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED: mm 1 PLC ±0.5 2 PLC ±0.1 3 PLC ±0.04 4 PLC ±0.001		APVD J.YIN	12NOV2021	NAME PLUG SUB-ASSEMBLY HVP-HD1400	
PERIPHERAL FINISH		PRODUCT SPEC 108-160407		SIZE A1	
		APPLICATION SPEC 116-160223		CAGE CODE 00779	
		WEIGHT		DRAWING NO. C=2399663	
		CUSTOMER DRAWING		RESTRICTED TO A1	
		SCALE 2:1		SHEET 1 OF 3	
				REV A1	

REVISIONS					
#	LYR	DESCRIPTION	DATE	OWN	APVD
		SEE SHEET 1			



2-★-1 AS SHOWN

3-2399663-3	M	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 3-2399679-3	FOLLOW 2399663-1 PLUG TPA	- M	- PA66-GF	- AQUA RED	(41.00)	- 1	2-7 1
3-2399663-2	L	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 3-2399679-2	FOLLOW 2399663-1 PLUG TPA	- L	- PA66-GF	- AQUA BROWN	(41.00)	- 1	2-7 1
3-2399663-1	K	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 3-2399679-1	FOLLOW 2399663-1 PLUG TPA	- K	- PA66-GF	- AQUA GREEN	(41.00)	- 1	2-7 1
2-2399663-9	J	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-9	FOLLOW 2399663-1 PLUG TPA	- J	- PA66-GF	- ORANGE	(41.00)	- 1	2-7 1
2-2399663-8	H	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-8	FOLLOW 2399663-1 PLUG TPA	- H	- PA66-GF	- YELLOW	(41.00)	- 1	2-7 1
2-2399663-7	G	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-7	FOLLOW 2399663-1 PLUG TPA	- G	- PA66-GF	- RED	(41.00)	- 1	2-7 1
2-2399663-6	F	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-6	FOLLOW 2399663-1 PLUG TPA	- F	- PA66-GF	- BROWN	(41.00)	- 1	2-7 1
2-2399663-5	E	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-5	FOLLOW 2399663-1 PLUG TPA	- E	- PA66-GF	- GREEN	(41.00)	- 1	2-7 1
2-2399663-4	D	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-4	FOLLOW 2399663-1 PLUG TPA	- D	- PA66-GF	- PURPLE	(41.00)	- 1	2-7 1
2-2399663-3	C	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-3	FOLLOW 2399663-1 PLUG TPA	- C	- PA66-GF	- BLUE	(41.00)	- 1	2-7 1
2-2399663-2	B	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	- 2-2399679-2	FOLLOW 2399663-1 PLUG TPA	- B	- PA66-GF	- NATURE	(41.00)	- 1	2-7 1
2-2399663-1	A	PLUG ASSEMBLY HVP-HD1400 TOOL ACCESS	2399675-1	PLUG HOUSING	-	PA66-GF	ORNGE	(41.00)	1	7
			2399676-1	SHIELD	-	COPPER ALLOY	AG PLATED		1	6
			2395531-2	CPA - TOOL ACCESS	-	PA66-GF	RED		1	5
			2395532-2	CPA SPRING - TOOL ACCESS	-	STAINLESS STEEL	-		1	4
			2383848-1	HVIL	-	COPPER	AG PLATED		1	3
			2399677-1	PERIPHERAL SEAL	-	SILICONE	GREEN		1	2
			2-2399679-1	PLUG TPA	A	PA66-GF	BLACK		1	1
TE ASSY NO.	CODE	DESCRIPTION	TE PART NO.	COMPONENT	CODE	MATERIAL	SURFACE COLOR	WEIGHT (g)	QTY	ITEM



FOR TOOL ACCESS

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN C.C.AO	12NOV2021	TE Connectivity	
DIMENSIONS: mm		CHK J.L.I	12NOV2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED: mm		APVD J.L.I	12NOV2021	NAME PLUG SUB-ASSEMBLY HVP-HD1400	
0 ALL 1 PLC 2 PLC 3 PLC 4 PLC		PRODUCT SPEC 11-11N 108-160407		SIZE A	
0.5 ±0.1 ±0.04 ±0.04 ±0.0001		APPLICATION SPEC 116-160223		CAGE CODE 00779	
NONE		WEIGHT		DRAWING NO C=2399663	
NONE		CUSTOMER DRAWING		RESTRICTED TO A1	
		SCALE 2:1		SHEET 2 OF 3	
				REV A1	

