

# WATER-TIGHT Incandescent Indicators



**T-1 3/4  
MIDGET  
FLANGE BASE**  
See lamp ratings  
on page J.


with RETAINED O-RING SEALS – TWO TERMINALS - FULLY INSULATED

WATER-TIGHT, OIL-TIGHT, DUST-TIGHT ON THE FACE OF THE PANEL

For mounting in 15/32" clearance hole

Conform to MIL-L-3661B

**MOUNT IN 15/32" CLEARANCE HOLE  
FRONT OF PANEL INSERTION  
WITH FIXED FLANGE**



367-8430-0931-503  
LH89/1; LC35RN2

## DIMMER TYPE




368-8430-0111-203  
LH89/1; LC36RD2

## Feature

- Anti-rotation (locked) construction: Provides for secure locking of the socket terminal assembly in the mounting bushing and of the center terminal to the insulating disc. The notched mounting bushing receives the matched insulating disc to prevent the rotation of the mounting bushing.

## QPL Listed

### FRONT MOUNTING



## MATERIALS AND FINISHES (367 series)

- **Mounting Bushing:** Aluminum, black anodize finish.
- **Internal-tooth Lockwasher and Mounting Nut:** Steel, cadmium plated with yellow iridescent chromate finish.
- **Terminals:** Brass, hot tinned, with elongated slots.
- **Lens:** High impact plastic.

## MATERIAL AND FINISHES (368 and 369 series)

- **Mounting Bushing:** Brass, black nickel finish.
- **Mounting Nut:** Brass, white nickel finish.
- **Internal-tooth Lockwasher:** Phosphor bronze, white nickel finish.
- **Terminals:** Brass, hot tinned with elongated slots.



**367 SERIES  
368 SERIES  
369 SERIES**

BASE PART NUMBER

| CAP PART NUMBERS | Type<br>Desig.                                | Part<br>No.  | Lens Cap<br>Color | COMPLETE ASSEMBLY PART NUMBERS |
|------------------|-----------------------------------------------|--------------|-------------------|--------------------------------|
|                  | <b>Stovepipe – Non Diffusing</b>              |              |                   |                                |
|                  | LC35RN2                                       | 128-0931-003 | Red               | 367-8430-0931-503              |
|                  | LC35GN2                                       | 128-0932-003 | Green             | 367-8430-0932-503              |
|                  | LC35YN2                                       | 128-0933-003 | Yellow (Amber)    | 367-8430-0933-503              |
|                  | LC35BN2                                       | 128-0934-003 | Blue              | 367-8430-0934-503              |
|                  | LC35CN2                                       | 128-0937-003 | Clear (Colorless) | 367-8430-0937-503              |
|                  | <b>Stovepipe – Translucent</b>                |              |                   |                                |
|                  | LC35RT2                                       | 128-0971-003 | Red               | 367-8430-0971-503              |
|                  | LC35GT2                                       | 128-0972-003 | Green             | 367-8430-0972-503              |
|                  | LC35YT2                                       | 128-0973-003 | Yellow (Amber)    | 367-8430-0973-503              |
|                  | LC35BT2                                       | 128-0974-003 | Blue              | 367-8430-0974-503              |
|                  | LC35WT2                                       | 128-0975-003 | White             | 367-8430-0975-503              |
|                  | <b>Convex Diffusing<br/>Complete Blackout</b> |              |                   |                                |
|                  | LC36RD2                                       | 160-0111-203 | Red               | 368-8430-0111-203              |
|                  | LC36GD2                                       | 160-0112-203 | Green             | 368-8430-0112-203              |
|                  | LC36YD2                                       | 160-0113-203 | Yellow (Amber)    | 368-8430-0113-203              |
|                  | LC36BD2                                       | 160-0114-203 | Blue              | 368-8430-0114-203              |
|                  | LC36CD2                                       | 160-0117-203 | Clear (Colorless) | 368-8430-0117-203              |
|                  | <b>Convex Diffusing<br/>Semi-Blackout</b>     |              |                   |                                |
|                  | LC37RD2                                       | 161-0111-203 | Red               | 369-8430-0111-203              |
|                  | LC37GD2                                       | 161-0112-203 | Green             | 369-8430-0112-203              |
|                  | LC37YD2                                       | 161-0113-203 | Yellow (Amber)    | 369-8430-0113-203              |
|                  | LC37BD2                                       | 161-0114-203 | Blue              | 369-8430-0114-203              |
|                  | LC37CD2                                       | 161-0117-203 | Clear (Colorless) | 369-8430-0117-203              |

Part numbers shown in gray are normally in inventory at your Dialight Distributor.

Order complete with lamp to be assured of receiving the indicator light and correct lamp together for immediate use.