

1

2

3

TABLE 1			SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE		PART NAME		MATERIAL		COLOR		△ QTY.	
△ 7283-7028-30 ETC.			① △ SEE TABLE 2		HOUSING		PBT		PBT		△ SEE TABLE 2		1	
			② 7157-4350		SPACER		PBT		PBT		NATURAL		1	
			③ △ 7137-2244-60		PACKING		△ SILICONE RUBBER		△ LIGHT GREEN		1		1	

TABLE 2			SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE		COLOR	
△			7283-7028, △		7183-7028		NATURAL	
△			7283-7028-10, △		7183-7028-10		DARK GRAY	
△			7283-7028-30, △		7183-7028-30		BLACK	
△			7283-7028-40, △		7183-7028-40		LIGHT GRAY	
△			7283-7028-50, △		7183-7028-50		ORANGE	
△			7283-7028-60, △		7183-7028-60		GREEN	
△			7283-7028-80, △		7183-7028-80		BROWN	
△			7283-7028-90, △		7183-7028-90		BLUE	

NOTES

1. MATING PART NO. : 7282-7028-30 ETC.

2. APPLICABLE TERMINAL NO. : 7116-4025 ETC.


3. APPLICABLE RUBBER STOPPER NO. : 7158-3006-90 ETC.

注 記

1. かん合相手品番 : 7282-7028-30 ETC.

2. 適用ターミナル品番 : 7116-4025 ETC.

3. 適用ゴム検品番 : 7158-3006-90 ETC.



△ 07.08.03		CHANGED FORM, ETC.		C07-Z830		K. S	
△ 03.04.14		CHANGED NAME & CORRECTION OF A CLERICAL ERROR		C03-X273		K. O	
△ 98.01.13		CHANGED MATERIAL, NOTES & PART NO. △		C97-N786		A. A	
△ 96.10.22		CHANGED FORM & ADDED PART NO.		C96-M949		M. T	
89.09.13		NEW		C89-L966		M. T	
LET		REVISION RECORD		NO.		CHKD	
		GENERAL TOLERANCE		10MAX		50MAX	
A		±0.15		±0.2		±0.3	
B		±0.2		±0.3		±0.5	
(C)		±0.3		±0.5		±0.8	
SPECIFIED		MASS		±30'		±30'	

CUSTOMER		CUSTOMER PART NO.		CUSTOMER DWG NO.	
OFFICE		TRIAL PART NO.		VENDOR NO.	
DWG TYPE		DWG SOURCE		DWG DATE	
R		NEW		89.09.19	
APPROVED		CHECKED		DESIGN	
△ 型		△ 1		SAMEJIMA M. MORAL	
07.08.03		07.08.03		89.06.21	
g		g		07.08.03	

PART NO. CH. CODE		△ 7283-7028-30 ETC.	
DWG NO.		7283-7028-30:R	
SET DWG NO.		7283-7028-30:R	
NAME		△ 2. 3 II 2P SEALED CONNECTOR	
SPEC.		HOUSING FEMALE SUB ASSEMBLY	
TREAT. & FIN.		ISSUE MARK	
YAZAKI CORPORATION		YAZAKI CORPORATION	