


Miniature Neon Indicators WITH BUILT-IN RESISTOR

FOR MOUNTING IN 11/16" CLEARANCE HOLE

For materials and finishes of products in this group, see page 53D.




T-3 1/4
B1A (NE-51)
B2A (NE-51H)
MINIATURE BAYONET BASE


See lamp ratings
on page L.

Recognized under the component
program of Underwriters' Laboratories Inc.


75W., 125V
75W., 250V




52-0463-0991-311
Screw-in lens cap



95-0408-0931-341
Screw-in lens cap



132-1363-0991-311
Screw-in lens cap



135-5708-1431-341
Screw-in lens cap

WITH SCREW-IN LENS CAPS

52 SERIES
95 SERIES
132 SERIES
135 SERIES

solder terminals	screw terminals	quick connect terminals	solder terminals ■

BASE PART NUMBERS

105-125VAC-DC*	95-0408-09-341	95-1308-09-341	95-5708-09-341	95-9108-09-142
110-125VAC†	95-0463-09-311	95-1363-09-311	95-5763-09-311	95-9163-09-112
210-250VAC-DC†	95-9463-09-361	95-9363-09-361	95-5863-09-361	95-9263-09-162

CAP PART NUMBERS	VOLTAGES	COMPLETE ASSEMBLY PART NUMBERS			
52-0991 stovepipe internal fluting	105-125V AC-DC 110-125 VAC 210-250V AC-DC	52-0408-0991-341 52-0463-0991-311 52-9463-0991-361	52-1308-0991-341 52-1363-0991-311 52-9363-0991-361	52-5708-0991-341 52-5763-0991-311 52-5863-0991-361	52-9108-0991-142 52-9163-0991-112 52-9263-0991-162
95-0931 stovepipe transparent	105-125V AC-DC 110-125 VAC 210-250V AC-DC	95-0408-0931-341 95-0463-0931-311 95-9463-0931-361	95-1308-0931-341 95-1363-0931-311 95-9363-0931-361	95-5708-0931-341 95-5763-0931-311 95-5863-0931-361	95-9108-0931-142 95-9163-0931-112 95-9263-0931-162
132-0991 stovepipe internal fluting	105-125V AC-DC 110-125 VAC 210-250V AC-DC	132-0408-0991-341 132-0463-0991-311 132-9463-0991-361	132-1308-0991-341 132-1363-0991-311 132-9363-0991-361	132-5708-0991-341 132-5763-0991-311 132-5863-0991-361	132-9108-0991-142 132-9163-0991-112 132-9263-0991-162
135-1431 cylindrical transparent	105-125V AC-DC 110-125 VAC 210-250V AC-DC	135-0408-1431-341 135-0463-1431-311 135-9463-1431-361	135-1308-1431-341 135-1363-1431-311 135-9363-1431-361	135-5708-1431-341 135-5763-1431-311 135-5863-1431-361	135-9108-1431-142 135-9163-1431-112 135-9263-1431-162

* Standard brightness
† High brightness

■ These units are designed for commercial application where military standards are not required.

For legends on flat faced lens, see page P.

Part numbers shown in gray are normally in inventory at your Dialight Distributor.