


22mm LED Illuminated Metal Flush Operators



Certified for
NEMA Type 4X
12 environment.

Flush Momentary

with bulb, bulb holder
and mounting bracket



**SAMPLE
ASSEMBLY**



For installation of a metal operator in the plastic enclosure a Cat No. ADW washer is required.



Replacement bulbs
available.
See page 39.

Color

Voltage

Cat No.

12V AC/DC

☐	White	12V AC/DC	2ALF1LB-012
☒	Green	12V AC/DC	2ALF3LB-012
☒	Red	12V AC/DC	2ALF4LB-012
☒	Amber	12V AC/DC	2ALF5LB-012
☒	Blue	12V AC/DC	2ALF6LB-012
☐	Clear	12V AC/DC	2ALF7LB-012
☒	Yellow	12V AC/DC	2ALF8LB-012

24V AC/DC

☐	White	24V AC/DC	2ALF1LB-024
☒	Green	24V AC/DC	2ALF3LB-024
☒	Red	24V AC/DC	2ALF4LB-024
☒	Amber	24V AC/DC	2ALF5LB-024
☒	Blue	24V AC/DC	2ALF6LB-024
☐	Clear	24V AC/DC	2ALF7LB-024
☒	Yellow	24V AC/DC	2ALF8LB-024

48V AC/DC

☐	White	48V AC/DC	2ALF1LB-048
☒	Green	48V AC/DC	2ALF3LB-048
☒	Red	48V AC/DC	2ALF4LB-048
☒	Amber	48V AC/DC	2ALF5LB-048
☒	Blue	48V AC/DC	2ALF6LB-048
☐	Clear	48V AC/DC	2ALF7LB-048
☒	Yellow	48V AC/DC	2ALF8LB-048

110V AC

☐	White	110V AC	2ALF1LB-110
☒	Green	110V AC	2ALF3LB-110
☒	Red	110V AC	2ALF4LB-110
☒	Amber	110V AC	2ALF5LB-110
☒	Blue	110V AC	2ALF6LB-110
☐	Clear	110V AC	2ALF7LB-110
☒	Yellow	110V AC	2ALF8LB-110

110V DC

☐	White	110V DC	2ALF1LB-110D
☒	Green	110V DC	2ALF3LB-110D
☒	Red	110V DC	2ALF4LB-110D
☒	Amber	110V DC	2ALF5LB-110D
☒	Blue	110V DC	2ALF6LB-110D
☐	Clear	110V DC	2ALF7LB-110D
☒	Yellow	110V DC	2ALF8LB-110D

230V AC

☐	White	230V AC	2ALF1LB-230
☒	Green	230V AC	2ALF3LB-230
☒	Red	230V AC	2ALF4LB-230
☒	Amber	230V AC	2ALF5LB-230
☒	Blue	230V AC	2ALF6LB-230
☐	Clear	230V AC	2ALF7LB-230
☒	Yellow	230V AC	2ALF8LB-230

230V DC


☐	White	230V DC	2ALF1LB-230D
☒	Green	230V DC	2ALF3LB-230D
☒	Red	230V DC	2ALF4LB-230D
☒	Amber	230V DC	2ALF5LB-230D
☒	Blue	230V DC	2ALF6LB-230D
☐	Clear	230V DC	2ALF7LB-230D
☒	Yellow	230V DC	2ALF8LB-230D

22mm LED Illuminated Metal Flush Operators


Dimensional Drawings

All dimensions shown in millimeters.
To convert to inches multiply by 0.03937

Flush Momentary



Switch Contacts (sold separately)



- Heavy-duty contact blocks with mounting screws. Blocks can be stacked 2 blocks across by 3 blocks deep for a total of 6 circuits.
- Contact blocks are available with silver contacts or gold plated contacts
- Self-wiping contacts

Panel Mount

Normally Open Silver	S1
Normally Closed Silver	S2
Normally Open Gold Plated	S3
Normally Closed Gold Plated	S4


Base Mount*

Normally Open Silver	S5
Normally Closed Silver	S6
Normally Open Gold Plated	S7
Normally Closed Gold Plated	S8

* For use with non-illuminated operators in thermoplastic or aluminum enclosures listed on pages 30 and 36-37.

Exploded Assembly View

- Up to four switch contacts can be installed with any Illuminated operator.
- Switch contacts and operators are sold separately. Preassembled push buttons are available on request.



For maintained or alternate action use Cat No. 2PPM.