

780-518

"Marshal Bean" Protective Rubber Cover

Universal D-Subminiature

for MIL-DTL-24308 Connectors



*"To Protect
and to Serve"*

780-518-15P G 12 - 03 C

Product Series _____

Basic Number _____

Shell Size (Table I) _____

Attachment Rope _____
G = Nylon Rope
(Omit for None)

C = Conductive
(Omit for Standard)

Attachment Type (Table II) _____

Attachment Length in Inches
($\pm .250$ (6.35) Inch) _____




TABLE I: SHELL SIZE & COVER DIMENSIONS

Shell Size	A	B	C	D
09S	.610 (15.5)	.280 (7.1)	.220 (5.6)	.820 (20.8)
09P	.650 (16.5)	.330 (8.4)	.230 (5.8)	.820 (20.8)
15S	.940 (23.9)	.280 (7.1)	.240 (6.1)	1.260 (32.0)
15P	.970 (24.6)	.330 (8.4)	.240 (6.1)	1.260 (32.0)
25S	1.480 (37.6)	.280 (7.1)	.250 (6.4)	1.760 (44.7)
25P	1.500 (38.1)	.330 (8.4)	.250 (6.4)	1.780 (45.2)
37S	2.120 (53.8)	.280 (7.1)	.230 (5.8)	2.290 (58.2)
37P	2.150 (54.6)	.330 (8.4)	.230 (5.8)	2.290 (58.2)
50S	2.030 (51.6)	.390 (9.9)	.240 (6.1)	2.170 (55.1)
50P	2.050 (52.0)	.450 (11.4)	.230 (5.8)	2.230 (56.6)

**TABLE II:
ATTACHMENT
TYPE**

Dash No.	E Dia $\pm .010$ (0.3)
00	No Terminal
01	.140 (3.6)
02	.182 (4.6)
03	.191 (4.9)
04	.197 (5.0)
05	.167 (4.2)
06	.125 (3.2)
07	.218 (5.5)
09	.156 (4.0)
WS	With Strap
SK	Slip Knot

NOTES:

- Cover Identified in area shown.
- Metric dimensions (mm) are indicated in parentheses.
- This series of covers is similar to Bean Rubber Mfg. Co. BP-D Subminiature Series, same Dash No.,
i.e.: BP-DAM15P-WS-L6 equivalent to 780-518-15PG6-WS
- Standard material contains trace amounts of sulfur (a vulcanizing agent) which is known to contribute to degradation/corrosion of silver plated components such as braid, etc. Specify MOD Code suffix -675 for sulfur-free material.