






RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
SINGLE SIDED APPLICATIONS





DETAIL H
RECOMMENDED CONNECTOR LAYOUT
4X INDIVIDUALLY

CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)


TITLE SFP28 1X4 CAGE,W/LIGHT PIPE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 22277301 1X4YD			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SIZE: A4
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SCALE: 1:1
			.XXX±0.10		SHEET:2/4
					REV:A

RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
BELLY TO BELLY APPLICATIONS




CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)


TITLE SFP28 1X4 CAGE,W/LIGHT PIPE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 22277301 1X4YD			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SIZE: A4
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:3/4
			.XXX±0.10		REV:A




SCALE: 1:1




RECOMMENDED BEZEL DESIGN
SINGLE SIDED APPLICATIONS



SECTION A-A




RECOMMENDED BEZEL DESIGN
BELLY TO BELLY APPLICATIONS



SECTION A-A

TITLE SFP28 1X4 CAGE,W/LIGHT PIPE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP28 22277301 1X4YD			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SIZE: A4
QG.CHEN.	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:4/4
			.XXX±0.10		REV:A



SCALE: 1:1