





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C2	REVISED PER ECO-11-005027	11MAR11	RK	HMR

- ① MATERIAL: POLYESTER, BLACK.
- ② OBSOLETE PART NUMBER.
- ③ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



2	44.76	43.74	51.18	47.37	68	1-104891-1
	[1.762]	[1.722]	[2.015]	[1.865]		
3	65.08	64.06	71.50	67.69	100	1-104891-0
	[2.562]	[2.522]	[2.815]	[2.665]		
	58.73	57.71	65.15	61.34	90	104891-9
	[2.312]	[2.272]	[2.565]	[2.415]		
	52.38	51.36	58.80	54.99	80	104891-8
	[2.062]	[2.022]	[2.315]	[2.165]		
	46.03	45.01	52.45	48.64	70	104891-7
	[1.812]	[1.772]	[2.065]	[1.915]		
	39.68	38.66	46.10	42.29	60	104891-6
	[1.562]	[1.522]	[1.815]	[1.665]		
33.33	32.31	39.75	35.94	50	104891-5	
[1.312]	[1.272]	[1.565]	[1.415]			
26.98	25.96	33.82	29.59	40	104891-4	
[1.062]	[1.022]	[1.315]	[1.165]			
20.63	19.61	27.05	23.24	30	104891-3	
[.812]	[.772]	[1.065]	[.915]			
14.28	13.26	20.70	16.89	20	104891-2	
[.562]	[.522]	[.815]	[.665]			
7.92	6.91	14.35	10.54	10	104891-1	
[.312]	[.272]	[.565]	[.415]			
	D	C	B	A	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN CIR J. CASTAGNA	23/JUN/93	 TE Connectivity	
		APP'D J. HERRINGTON	24/JUN/93		
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.36(015) 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —		NAME TERMINATING COVER AMPMODU 50/50 GRID	
		PRODUCT SPEC 108-1443 APPLICATION SPEC 114-7010		SIZE CASE CODE DRAWING NO A1 00779 C=104891	
MATERIAL 		WEIGHT —		RESTRICTED TO —	
		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV C2	