




REV.	DESCRIPTION

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

- Notes:
- * QC Important Dimensions To Check.
 - * Waterproof Rate: IP68
(Mated, by Applying O-ring and Potting Material)
 - * Male Pin: Copper Alloy, Gold Plated.

UNIT:mm	
TOLERANCE	±0.5MM







TITLE FLO OK FI CONNECTOR			
SCALE	Free	SHEET	1 OF 2
REV.	01	SIZE	A4
QC :Inspection Item			

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	FLKB-XXFGMS-XCP-2XX
DWG NO	FLKB-XXFGMS-XCP-2XX
CUSTOMER	ALTW

DRAWN BY	Ouyang
CHECKED BY	Mafei
APPROVED BY	Jerry

DATE	2018/09/04
DATE	2018/09/04
DATE	2018/09/04

	1	2	3	4	5	6	7	8
F								
E	OK-SERIES CABLE COLLET(CABLE OD)				FLKB-XXFGMS-XCP-2XX			
	CABLE CLAMP SET		CABLE DIA RANGE					
	TYPE	CODE ①	MAX	MIN				
	FLKB-XXFGMS-XCP-2XX	03	3.0	2.8				CABLE OD ①
		05	3.6	3.4				KEY POINT ②
06		4.0	3.8				PIN CONFIGURATION ③	
09		4.7	4.5				SIZE(CONNECTOR)	
D	KEY POINT							
C	CODE ②	G	A	B	C	D		
		0°	30°	45°	60°	95°		
	GRAPHIC							
B	PIN CONFIGURATION (Solder Definition) ③							
	GRAPHIC							
	2 PIN	3 PIN	4 PIN	5 PIN	6 PIN	7 PIN	9 PIN	
A	UNIT:mm		TITLE FLO OK FI CONNECTOR		ITEM NO FLKB-XXFGMS-XCP-2XX		DRAWN BY Ouyang	
TOLERANCE ±0.5MM		SCALE Free		SHEET 2 OF 2		DWG NO FLKB-XXFGMS-XCP-2XX		CHECKED BY Mafei
		REV. 01		SIZE A4		CUSTOMER ALTW		APPROVED BY Jerry
				QC :Inspection Item				DATE 2018/09/04
	1	2	3	4	5	6	7	8

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.