

Set Han3A LC duplex AC plug SM GOF



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 09 57 508 0501 000 |
| Specification | Set Han3A LC duplex AC plug SM GOF |
| HARTING eCatalogue | https://b2b.harting.com/09575080501000 |

Identification

| | |
|-----------------------------|------------------|
| Category | Connectors |
| Series | LC duplex Hybrid |
| Element | Cable connector |
| Type of contact | LC contact |
| Description of the contact | Singlemode |
| Type of hood/housing | Hood |
| Description of hood/housing | Straight |

Version

| | |
|-----------------------|---------------|
| Size | 3 A |
| Number of contacts | 2 |
| Contact configuration | L1, PE, N |
| further contacts | + 3x 300 V AC |

Technical characteristics

| | |
|--|----------------|
| Limiting temperature | -40 ... +70 °C |
| Degree of protection acc. to IEC 60529 | IP65 IP67 |
| Cable diameter | 6 ... 9 mm |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
| Surface (hood/housing) | Powder-coated |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|--|
| Colour (hood/housing) | Black |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(b) / 6(b)-II: Lead as an alloying element in aluminium containing up to 0,4 % lead by weight / Lead as an alloying element in aluminium for machining purposes with a lead content up to 0,4 % by weight 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Antimony trioxide Lead Nickel Naphthalene |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R26 |

Specifications and approvals

| | |
|-----------|--------|
| Approvals | DNV GL |
|-----------|--------|

Commercial data

| | |
|--------------------------------|---------------------------------------|
| Packaging size | 1 |
| Net weight | 156 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| GTIN | 5713140072749 |
| ETIM | EC002636 |
| eCl@ss | 27440113 Rectangular connectors (set) |