

# 9001SK43J1R

Harmony 9001SK, illuminated selector switch head, plastic, standard handle, red, 30mm, 3 positions, stay put, 110-120V



## Main

|                           |                                                              |
|---------------------------|--------------------------------------------------------------|
| Bezel material            | Plastic                                                      |
| Device short name         | K                                                            |
| Enclosure type            | Dust and oil resistant weatherproof enclosure indoor/outdoor |
| Mounting diameter         | 1.18 in (30 mm)                                              |
| Product or Component Type | Head for illuminated selector switch                         |
| Range of Product          | Harmony 9001SK                                               |

## Complementary

|                               |                                                                        |
|-------------------------------|------------------------------------------------------------------------|
| Bulb base                     | BA 9s                                                                  |
| Contacts type and composition | Without contact block                                                  |
| Light block supply            | Via transformer 120 V AC 50/60 Hz<br>Via transformer 110 V AC 50/60 Hz |
| Operator position information | 3 positions                                                            |
| Operator profile              | Standard handle                                                        |
| Operator profile              | 1 projecting push-button                                               |
| Size                          | 30 mm                                                                  |
| Type of operator              | Maintained                                                             |

## Environment

|                           |                                                                   |
|---------------------------|-------------------------------------------------------------------|
| NEMA Degree of Protection | NEMA 1/2/3/3R/4/4X/6/12/13                                        |
| Product Certifications    | CE<br>CSA LR24590 class 3211 03<br>UL listed file E42259 CCN NKCR |

## Ordering and shipping details

|                       |                     |
|-----------------------|---------------------|
| Category              | 21429-9001 SK,SKY   |
| Discount Schedule     | CS1                 |
| GTIN                  | 785901960096        |
| Nbr. of units in pkg. | 1                   |
| Package weight(Lbs)   | 6.56 oz (185.973 g) |
| Returnability         | No                  |
| Country of origin     | MX                  |

## Packing Units

|                        |                      |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE                  |
| Package 1 Height       | 5.08 in (12.903 cm)  |
| Package 1 width        | 2.00 in (5.08 cm)    |
| Package 1 Length       | 12.90 in (32.774 cm) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                             |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                       |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                              |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                                                         |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                                                      |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                               |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                                                                |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|