


- NOTES:
- 1. ALL PARTS TO BE BULK PACKED.
 - 2. CONTACTS ARE SUPPLIED UNASSEMBLED
 - 3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE
 - 4. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS

ASS'Y P/N	GROMMET SIZE
W6380-XPG-P-311	CABLE O.D. .09-.14 [2.3 - 3.6]
W6380-XPG-P-315	CABLE O.D. .15-.17 [3.8 - 4.3]
W6380-XPG-P-318	CABLE O.D. .18-.20 [4.6 - 5.1]
W6380-XPG-P-321	CABLE O.D. .21-.23 [5.3 - 5.8]

ASSEMBLY P/N	CONTACTS
W6380-2PG-P-3XX	2 #16
W6380-3PG-P-3XX	3 #16
W6380-4PG-P-3XX	4 #16
W6380-XPG-P-3XX	




GROMMET SIZE FOR
SINGLE GROMMET OR
"DC" FOR DAISY CHAIN

NUMBER OF CONTACTS







SHOWN ASSEMBLED
FOR CUSTOMER REFERENCE ONLY

DAISY CHAIN GROMMETS
FOR W6380-XPG-P-3DC
.125 I.D. FOR CABLES .09-.14 [2.3 - 3.6] O.D.
.188 I.D. FOR CABLES .18-.20 [4.6 - 5.1] O.D.
.250 I.D. FOR CABLES .24-.26 [6.1 - 6.6] O.D.




MATING FACE
W6380-2PG-P-3XX SHOWN




GROMMET
MAT'L: SANTOPRENE, BLACK

BACKSHELL
MAT'L: UV PBT, BLACK


(2-4) #16 PIN CONTACT, CRIMP
MAT'L: COPPER ALLOY, GOLD PLATED




WIRING END
W6380-2PG-P-3XX SHOWN
WITHOUT HARDWARE



WIRING END
W6380-2PG-P-3XX



WIRING END
W6380-3PG-P-3XX



WIRING END
W6380-4PG-P-3XX

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL
INFORMATION PROPRIETARY TO CONXALL
CORPORATION. ANY REPRODUCTION,
DISCLOSURE, OR USE OF THIS
DOCUMENT /INFORMATION IS EXPRESSLY
PROHIBITED UNLESS AUTHORIZED IN
WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	02-28-20	RELEASED PER PDR 16014-7	
	PNK	11-25-19	BACKSHELL P/N 6284 CHANGES TO 6284V4	
	PNK	05-10-19	PDR 16014	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: PNK	DATE: 05-10-19
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS. UNLESS OTHERWISE SPECIFIED TOLERANCES 3 PLACE DECIMALS ±.010 ANGLES ±1° FRACTIONS ±1/16 = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			CHECKED BY:	 601 E. WILDWOOD VILLA PARK, IL 60181
APPROVED BY:			APPROVED BY:	
SCALE NTS			SIZE B	
FILE: W6380-XPG-P-3XX			SHEET 1 OF 1	
DIRECTORY: SLW			TITLE: CABLE-END ASSEMBLY 2-4 #16 PIN CONTACTS, CRIMP INSTA-CLOCK™ MINI-CON-X STANDARD PRODUCT	
PART NUMBER: W6380-XPG-P-3XX			CUSTOMER:	REV A