








ISOMETRIC VIEWS
SCALE 3:1



SECTION Z-Z


2289730-1 AS SHOWN

- 1 HOUSING - POLYESTER PBT, COLOR: SEE TABLE, GLASS FILLED
CPA - POLYESTER PBT, TRAFFIC RED, GLASS FILLED
SECONDARY LOCK - POLYESTER PBT, WATER BLUE, GLASS FILLED
- 2 CABLE ASSEMBLY: SEE TABLE.
- 3 FEMALE INTERFACE PER ISO-20860-1, ISO-20860-2, SAE/USCAR-17, SAE/USCAR-18.
- 4 SECONDARY LOCK AND CPA IN PRESET POSITION. IF SECONDARY LOCK IS IN FULLY LOCKED POSITION, SEE 408-162008 FOR INSTRUCTIONS TO RESET SECONDARY LOCK TO PRESET POSITION.
- 5 CLIP SLOT PER SAE/USCAR-18, EWCAP-005-7.


WITHOUT CPA	(SOLD SEPARATELY) SEE SHEET 2	Z	PER DETAIL Z	WATER BLUE	4-2289730-0	
		N	PER DETAIL N	PASTEL GREEN	3-2289730-3	
		M	PER DETAIL M	PASTEL ORANGE	3-2289730-2	
		L	PER DETAIL L	CARMINE RED	3-2289730-1	
		K	PER DETAIL K	CURRY	3-2289730-0	
		I	PER DETAIL I	BEIGE	2-2289730-9	
		H	PER DETAIL H	HEATHER VIOLET	2-2289730-8	
		G	PER DETAIL G	BLUE GREY	2-2289730-7	
		F	PER DETAIL F	NUT BROWN	2-2289730-6	
		E	PER DETAIL E	LEAF GREEN	2-2289730-5	
		D	PER DETAIL D	CLARET VIOLET	2-2289730-4	
		C	PER DETAIL C	SIGNAL BLUE	2-2289730-3	
		B	PER DETAIL B	CREAM	2-2289730-2	
		A	PER DETAIL A	JET BLACK	2-2289730-1	
		WITH CPA	Z	PER DETAIL Z	WATER BLUE	2-2289730-0
N			PER DETAIL N	PASTEL GREEN	1-2289730-3	
M			PER DETAIL M	PASTEL ORANGE	1-2289730-2	
L			PER DETAIL L	CARMINE RED	1-2289730-1	
K			PER DETAIL K	CURRY	1-2289730-0	
I			PER DETAIL I	BEIGE	2289730-9	
H			PER DETAIL H	HEATHER VIOLET	2289730-8	
G			PER DETAIL G	BLUE GREY	2289730-7	
F			PER DETAIL F	NUT BROWN	2289730-6	
E			PER DETAIL E	LEAF GREEN	2289730-5	
D			PER DETAIL D	CLARET VIOLET	2289730-4	
C			PER DETAIL C	SIGNAL BLUE	2289730-3	
B			PER DETAIL B	CREAM	2289730-2	
A		PER DETAIL A	JET BLACK	2289730-1		
CPA	CABLE ASSEMBLY QTY=1		CODING REF	KEYING	CODING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. J. HARDY CHK D. J. HARDY APVD D. J. HARDY	14APR2015 14APR2015 14APR2015	 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		PRODUCT SPEC 108-32137 APPLICATION SPEC 114-32145	
				FEMALE KIT, CPA, CLIP SLOT, 1 POSITION, FAKRA AUTOMATED	
MATERIAL		WEIGHT		SIZE	CAGE CODE
		-		A1	-
		RESTRICTED CUSTOMER		DRAWING NO	RESTRICTED TO
				C=2289730	
				SCALE	SHEET
				8:1	1 OF 2
					REV A


REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
-	-	SEE SHEET 1	-	-	-




2289730-1 AS SHOWN
SCALE 5:1




DETAIL A
SCALE 4:1




DETAIL B
SCALE 4:1




DETAIL C
SCALE 4:1




DETAIL D
SCALE 4:1




DETAIL E
SCALE 4:1




DETAIL F
SCALE 4:1




DETAIL G
SCALE 4:1




DETAIL H
SCALE 4:1




DETAIL I
SCALE 4:1




DETAIL K
SCALE 4:1




DETAIL L
SCALE 4:1



DETAIL M
SCALE 4:1



DETAIL N
SCALE 4:1



DETAIL Z
SCALE 4:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. J. HARDY 14APR2015	 TE Connectivity	
DIMENSIONS:		CHK D. J. HARDY 14APR2015		
mm		APVD D. J. HARDY 14APR2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ±		108-32137	NAME FEMALE KIT, CPA, CLIP SLOT, 1 POSITION, FAKRA AUTOMATED	
1 PLC ±		APPLICATION SPEC		
2 PLC ±		114-32145	SIZE A1	
3 PLC ±		WEIGHT		
4 PLC ±		RESTRICTED CUSTOMER	SCALE 5:1	
ANGLES ±				
FINISH			SHEET 2 OF 2	
MATERIAL				
			REV A	