



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2019/04/10	Bovan Lu	Initial Released.


Male Connector Position & Key Direction



Female Connector Position & Key Direction



※ This drawing is common drawing of series products.
The figure only shows individual position and key direction of male/female connectors.
Specific state of C1,2,3 connectors depends on part number. (see sheet 2/3)



Note:
* IP: IP68 (IM/24Hr.)
* Connector: Thermoplastic
* Pin: Copper Alloy
* Nut: Metal
* Other:

UNIT:mm			TITLE M12, A-Code, Y-Adaptor			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO		DRAWN BY Bovan Lu		DATE 2019-04-10				
TOLERANCE ±0.5mm								SCALE 1:1		SIZE A4		SHEET 1 OF 3		DWG NO YA-XXXX-XXXX-XXXX-XX		CHECKED BY Neo Tsai
			REV. A		WC-REV. A.27			QC: Inspection item		CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-04-10		

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Y A - A X X X - A X X X - A X X X - X X

-01: All connectors have the same number of pins.

C1 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin

C1 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin

C2 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin

C2 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin

C3 Connector Type

03: 3 pin
04: 4 pin
:
12: 12 pin

C3 Gender

M: Male Connector, Male Pin
F: Female Connector, Female Pin

UNIT:mm

TOLERANCE

TITLE M12, A-Code, Y-Adaptor			
SCALE 1:1	SIZE A4	SHEET 2 OF 3	
REV. A	WC-REV. A.27	QC: Inspection item	

Amphenol LTW

安費諾亮泰企業股份有限公司


ITEM NO	DWG NO YA-XXXX-XXXX-XXXX-XX
CUSTOMER ALTW	

DRAWN BY Bovan Lu	CHECKED BY Neo Tsai
APPROVED BY Max Yang	

DATE 2019-04-10	DATE 2019-04-10
DATE 2019-04-10	

	A - code						
	3 Pin	4 Pin	5 Pin	6 Pin	8 Pin	10 Pin	12 Pin
Male							
Female							
Pin Out	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color	Pin# Color
	Pin1 Black Pin3 White Pin4 Blue	Pin1 Black Pin2 White Pin3 Blue Pin4 Green	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin6 Red Pin7 Gray	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange Pin9 Brown Pin10 Purple	Pin1 Black Pin2 White Pin3 Blue Pin4 Green Pin5 Red Pin6 Gray Pin7 Yellow Pin8 Orange Pin9 Brown Pin10 Purple Pin11 White/Red Pin12 Pink

Pin Assignments Front View



UNIT:mm TOLERANCE		TITLE M12, A-Code, Y-Adaptor			ITEM NO		DRAWN BY Bovan Lu		DATE 2019-04-10	
		SCALE 1:1	SIZE A4	SHEET 3 OF 3	DWG NO YA-XXXX-XXXX-XXXX-XX		CHECKED BY Neo Tsai		DATE 2019-04-10	
		REV. A	WC-REV. A.27	QC:Inspection item	CUSTOMER ALTW		APPROVED BY Max Yang		DATE 2019-04-10	
		Amphenol LTW 安費諾亮泰企業股份有限公司								