

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2000

© COPYRIGHT 2000

BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	RELEASED AS PER ECR-09-005170	05.MAR.2009	GG	TS
	B4	REVISED PER ECR-17-013084	11JAN2018	SRG	MKO

NOTES


- 1 PACKAGING
PACKAGING QUANTITY:5 PIECES PER BOX
- 2 MATERIAL:HOUSING ALUMINIUM DIECASTING ALLOY
- 3 SURFACE:POWDER COATED-GREY
CORROSION PROTECTION-BLACK
- 4 VARNISH ON THE INSIDE NOT NECESSARY

PN 0-1 & 2-7





SCALE 1:2

PN 1-2 & 1-7




SCALE 1:2

PN 0-1 & 2-7



PN 1-2 & 1-7




OBSOLETE

2	2	2	2	INSULATING TAPE	COROPLAST TYP 303	-	GREY	7	PVC-SOFT
1	1	1	1	PROFILE SEAL	NEOPRENE	-	BLACK	6	-
2	-	-	2	CLIP BOLT	STAINLES STEEL	BLANK	-	5	-
1	-	-	-	HOOD	ALUMINIUM	HARD COAT	BLACK	4	-
-	1	-	-	HOOD	ALUMINIUM	-	GREY	3	-
-	-	-	1	HOOD	ALUMINIUM	HARD COAT	ALU COLORED	2	-
-	-	1	-	HOOD	ALUMINIUM	WITHOUT VARNISH	-	1	-
2-7	1-7	1-2	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO	REMARKS
				HA-K.10.STS.1.16.G					
				HA.10.STS.1.16.G					
				HA.10.STS.1.16.G					
				HA-K.10.STS.1.16.G					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

material_2

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
±

FINISH

finish_spec_2

DWN 23/02/2006

S.KUMAR

CHK 23/02/2006

R.SRINIVAS

APVD 23/02/2006

T.SCHNURPFIL

PRODUCT SPEC

108-74009

APPLICATION SPEC

114-74001

WEIGHT

-

NAME

HOOD
HA.10.STS.1.16.G

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-1102117

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE

1:1

SHEET

1 OF 1

REV

B4