





			0.4	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.57	33	1.20φ~1.30φ	6-316300-7
	OBSOLETE		0.4	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.57	24	0.90φ~1.15φ	6-316300-6
	OBSOLETE		0.4	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.06	15	0.64φ~0.89φ	6-316300-5
	OBSOLETE	 POKE-IN TAB APPLICABLE	0.4	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.06	10	0.35φ~0.63φ	6-316300-4
			0.5	穴無し (WITHOUT HOLE)	錫めっき仕上 (TIN PLATED)	4.57	24	0.90φ~1.15φ	2-316300-9
			0.5	穴無し (WITHOUT HOLE)	錫めっき仕上 (TIN PLATED)	4.06	15	0.64φ~0.89φ	2-316300-8
		 POKE-IN TAB NOT APPLICABLE	0.5	穴無し (WITHOUT HOLE)	錫めっき仕上 (TIN PLATED)	4.06	10	0.35φ~0.63φ	2-316300-7
	OBSOLETE			穴無し (WITHOUT HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.57	24	0.90φ~1.30φ	316300-9
	OBSOLETE			穴無し (WITHOUT HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.06	15	0.64φ~0.89φ	316300-8
	OBSOLETE			穴無し (WITHOUT HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.06	10	0.35φ~0.63φ	316300-7
			0.5	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.57	24	0.90φ~1.15φ	316300-6
			0.5	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.06	15	0.64φ~0.89φ	316300-5
		 POKE-IN TAB NOT APPLICABLE	0.5	穴有り (WITH HOLE)	錫めっき仕上 (TIN PLATED)	4.06	10	0.35φ~0.63φ	316300-4
	OBSOLETE			穴有り (WITH HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.57	24	0.90φ~1.30φ	316300-3
	OBSOLETE			穴有り (WITH HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.06	15	0.64φ~0.89φ	316300-2
	OBSOLETE			穴有り (WITH HOLE)	半田めっき仕上 (TIN-LEAD PLATED)	4.06	10	0.35φ~0.63φ	316300-1
		ポークイン部かん合 MATING TO POKE-IN	 "X" REF	 タブ穴 (HOLE IN TAB)	仕上 (FINISH)	 "A"	 I.Dマーク (I.D MARK)	 ワイヤーレンジ (導体径) {WIRE RANGE (BARE WIRE DIA)}	型番 (PART No.)

 TABLE 1

187 SERIES POSITIVE LOCK EX	STRAIGHT TYPE	173722-1
		173723-1
		173724-X
		173725-X
	FLAG TYPE	175019-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
MM



MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差



FINISH
仕上

DWN
Y.SUEMITSU
25.SEP.'01

CHK
M.SHINDO
25.SEP.'01

APVD
M.SHINDO
25.SEP.'01

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

 Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME
STD MAG-MATE POKE-IN
WITH .187 TAB

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-316300

RESTRICTED TO
—

SCALE
尺度 1:1

SHEET
2 OF 2

REV
F2