



								PANDUIT INSTALLATION TOOLS		
H-TAP PART NUMBER	H-TAP & CLEAR COVER KIT PART NUMBER	CONDUCTOR SIZES CODE WIRE (FLEX CABLE)				WIRE STRIP LENGTH	CRIMP DIE COLOR CODE	CT-930 CT-930CH CT-940CH* CT-2940*	CT-920 CT-920CH CT2920	CT-2931
		MAIN	TAP 1	TAP 2	TAP 3			CRIMP DIE NO./DIE INDEX NO. (# OF CRIMPS=1)		
HTCT8-8-1	HTWC8-8-1	8-14 (8-14)	8-14 (8-14)	--	--	19/32"	GREEN	CD-920H-8 PH8	CD-920H-8 PH8	CD-920H-8 PH8
HTCT6-6-1	HTWC6-6-1	6-10 (6-10)	6-14 (6-14)	--	--	11/16"	ORANGE	CD-920H-6 PH6	CD-920H-6 PH6	CD-920H-6 PH6
HTCT2-2-1	HTWC2-2-1	2-6 STR/SOL (2-8)	2-6 STR/SOL (2-8)	8-14 (8-14)	8-14 (8-14)	13/16"	BROWN	CD-920H-2 PH2	CD-920H-2 PH2	CD-920H-2 PH2
HTCT250-8-1	HTWC250-8-1	250-2 (4/0-2)	8-14 (8-14)	8-14 (8-14)	--	1"	PURPLE	CD-930H-250 PH25	-	CD-930H-250 PH25
HTCT250-2-1	HTWC250-2-1	250-2 (4/0-2)	2-6 STR/SOL (2-8)	8-14 (8-14)	--	1"	PURPLE	CD-930H-250 PH25	-	CD-930H-250 PH25
HTCT250-250-1	HTWC250-250-1	250-2 (4/0-2)	250-2 (4/0-2)	--	--	1"	PURPLE	CD-930H-250 PH25	-	CD-930H-250 PH25
*REQUIRES CD-940-DA ADAPTER										

- NOTES:
1. MATERIAL: ANNEALED HIGH CONDUCTIVITY COPPER, TIN PLATED
 2. FOR USE WITH COPPER OR TIN PLATED COPPER CONDUCTORS ONLY.
 3. ACCOMODATES CODE CABLE, SOLID WIRE (WHERE SPECIFIED), FLEX LOCOMOTIVE (DLO), AND FLEX CLASSES G, H & I.
 4. ANY SINGLE TAP OR COMBINATION OF TAPS MAY BE USED IN CONJUNCTION WITH MAIN WIRE PORT.
 5. UL LISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600V. TEMPERATURE RATING 90°C MAX.
 6. FLAME RETARDANT CABLE TIES (UL94 V-0 RATED NYLON WITH L.O.I.=28 MIN.) ARE PROVIDED WITH THE TAPS TO RETAIN THE WIRES IN POSITION FOR CRIMPING.
 7. TO ORDER H-TAP WITH INSULATING COVERS SEE PART NUMBERS IN TABLE.
 8. H-TAPS AND KITS ARE PACKAGED INDIVIDUALLY. (-1 PACKAGING CODE)



				CAD FILENAME/LAYERS				C41379_02	
								PANDUIT CORP TINLEY PARK, ILLINOIS	
								H-TAP SERIES COPPER COMPRESSION SMALL TAPS	
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .X (.XXX) ± .X (.XX) ± .03 ANGLES ± .X	
02	11/04	RGB		ADDED CT-2931 COLUMN TO THE TABLE				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
01	05/03	RWK	RLS	REMOVED BLACK COVER KIT NUMBERS	10818	LSM	JAC	DRAWN BY RWK	MAT'L: NONE
00	04/03	RWK	RLS	DRAWING RELEASED	10794	LSM	JAC	DATE 4/21/03	SEE NOTES
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	CHK'D RLS	DWG C41379 B SIZE