



STRAIGHT BULKHEAD JACK PANEL SEAL
R142.334.700
CRIMP TYPE CABLE 0.8/3.7


Series : BNC 75 HDTV


PANEL CUT OUT


	mm	
	Maxi	mini
A	12.8	12.7
B	10.9	10.8



Scale 1/1



All dimensions are in mm.

COMPONENTS	MATERIALS	PLATING (μm)
BODY	BRASS	NICKEL 2
CENTER CONTACT	BERYLLIUM COPPER	NPGR
OUTER CONTACT		
INSULATOR	PTFE	
GASKET	SILICONE RUBBER	
OTHERS PARTS	BRASS	NICKEL 2
-	-	-
-	-	-

Issue : 0836 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIAL 

STRAIGHT BULKHEAD JACK PANEL SEAL**CRIMP TYPE CABLE 0.8/3.7****R142.334.700**

Series : BNC 75 HDTV

PACKAGING

Standard	Unit	Other
100	'W' option	Contact us

ELECTRICAL CHARACTERISTICS

Impedance	75 Ω
Frequency	0-6 GHz
VSWR	1.05 + 0.0350 x F(GHz) Maxi
Insertion loss	0.1 $\sqrt{F}$ (GHz) dB Maxi
RF leakage	- (55* - F(GHz)) dB Maxi
Voltage rating	500 Veff Maxi
Dielectric withstanding voltage	1500 Veff mini
Insulation resistance	5000 M Ω mini

MECHANICAL CHARACTERISTICS

Center contact retention	
Axial force – Mating end	10 N mini
Axial force – Opposite end	10 N mini
Torque	NA N.cm mini

Recommended torque	
Mating	NA N.cm
Panel nut	370 N.cm
Clamp nut	NA N.cm
A/F clamp nut	0,0000 mm

Mating life	1000 Cycles mini
Weight	18,1600 g

ENVIRONMENTAL

Operating temperature	-65/+165 °C
Hermetic seal	NA Atm.cm3/s
Panel leakage	NA

SPECIFICATION**CABLE ASSEMBLY**

Stripping	a	b	c	d	e	f
mm	3,30	10,3	16,8	0,00	13,5	0,00

Assembly instruction : **Crimp 01**

Recommended cable(s)

DRAKA 0.8/3.7

BELDEN 1505A

CAE HD 08370

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off	136 N mini
- torque	NA N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.
R282.235.013	CRIMPING DIES	6.48
R282.249.000		6.48
R282.293.000	CRIMPING TOOL M22520/5-01	
R282.223.000	CRIMPING TOOL	

OTHER CHARACTERISTICS

* From 2 to 3GHz

Issue : 0836 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

