

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2001

© COPYRIGHT 2001

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
JDIST
-REVISIONS
変更

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
0		RELEASED	FJ00-1740-01	26SEP2001	S.Y	S.M
01		REVISED	FJD0-0298-03	27AUG2003	D.M	S.M

-1 : AS SHOWN (F/H)
-1 : 本図 (F/H)

列番号
ROW NO.キャップハウジング
CAP HOUSINGタブコンタクト
TAB CONTACTタップハウジング
TAP HOUSINGAMPマーク&シリーズマーク
AMP MARK & SERIES MARK回路番号
CIRCUIT No.テートコード
D/Cパネル加工推奨寸法図
RECOMMEND PANEL LAYOUT


-2 : AS SHOWN (P/M)
-2 : 本図 (P/M)
(SCALE 1:1)

注記

- 1、材料：ハウジング：ガラス入り熱可塑性ポリエステル樹脂、94V-0、黒
コンタクト：銅合金
2、メッキ：コンタクト：全面Ni下地 1.3μmMIN、接点部：金メッキ 0.38μmMIN

NOTE

- 1, MATERIAL; HOUSING: GLASS FILED THERMOPLASTIC, 94V-0, BLACK
CONTACT: COPPER ALLOY
2, FINISH; UNDER PLATE: Ni 1.3μm MIN, CONTACT AREA: Au 0.38μm MIN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS:
単位: ㎜MATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ± ±0.4
2 PLC ± ±3°
3 PLC ±
4 PLC ±
ANGLES ±

FINISH
仕上

DWN 09AUG2001

S. YOKOZEK

CHK 26SEP2001

D. MITSUGI

APVD 26SEP2001

S. MANABE

PRODUCT SPEC

108-5754

APPLICATION SPEC

取付適用規格

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, JapanNAME
名称DYNATAP CONN. 18P ASSY
-DYNAMIC 3100 -

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1376807

RESTRICTED TO

-

SCALE
尺度

2:1

SHEET

1

OF

1

REV

01