



REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED
B	REVISED PER ECN# T-16058	91APR25	Z. TEMAN
C	REVISED PER ECN T-16511	91JUL30	Z. TEMAN
D	REVISED PER ECN T-18956	94 Feb 25	35


PART No.	CONTACT	INTERFACE	COLOR CODE
DK-621-X411R	—	THREADED	N/A
DK-621-X411R-P	PIN	THREADED	
DK-621-X411R-S	SOCKET	THREADED	
DK-621-X433R	—	A	RED
DK-621-X433R-1P	PIN	A	
DK-621-X433R-1S	SOCKET	A	
DK-621-X435R	—	B	WHITE
DK-621-X435R-2P	PIN	B	
DK-621-X435R-2S	SOCKET	B	
DK-621-X437R	—	C	GREEN
DK-621-X437R-3P	PIN	C	
DK-621-X437R-3S	SOCKET	C	
DK-621-X439R	—	D	N/A
DK-621-X439R-4P	PIN	D	
DK-621-X439R-4S	SOCKET	D	



PLUG - THREADED
CONNECTOR
D-621-0411R



PLUG - BAYONET
CONNECTOR
D-621-0433R/0439R



RIGHT ANGLE
ADAPTER TUBE
D-600-0601




STRAIN RELIEF

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

DWG No. EXAMPLE X433R

-0433R .148 MAX. CABLE DIA ACCOMODATION
BRAID TERMINATOR D-600-0030

-1433R .180 MAX. CABLE DIA ACCOMODATION
BRAID TERMINATOR D-600-0056



CONTACT
D-602-0126
(D-602-0127)



BRAID
TERMINATOR
D-600-00XX

SPECIFICATION CONTROL DRAWING

© Raychem Corporation 1990

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.
METRIC DIMENSIONS ARE
IN BRACKETS.

DECIMALS

.XXX ± — [— mm]
.XX ± — [— mm]

ANGLES


.X ± —

WEIGHT

— lbs [— g]

DRAWN	J.B.K.	90 AUG 8
CHECKED	35	94 Feb
APPROVED	PJD	14-2-4
APPROVED		
CAD NAME	004951-1.DWG	

THIRD ANGLE
PROJECTION




Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
MENLO PARK, CALIFORNIA 94025

TITLE

RIGHT ANGLE
TRIAxIAL CONNECTOR PLUG
CONNECTOR KITS

SIZE	CODE IDENT. NO.	DWG. NO.	REV
A	06090	DK-621-X4XXR[-XX]	D
DO NOT SCALE THIS DRAWING			SHEET 1 OF 2



1.0 REFER TO THE FOLLOWING RAYCHEM SPECIFICATION CONTROL DRAWINGS (SCD) FOR INDIVIDUAL COMPONENT PERFORMANCE PARAMETERS, DIMENSIONS AND MATERIAL DETAIL:

D-621-0411R	CONNECTOR, TRIAXIAL, SUBMINIATURE THREADED COUPLED. FOR RIGHT ANGLE THREADED ADAPTER
D-621-0433R/0440R	CONNECTOR, TRIAXIAL, SUBMINIATURE BAYONET COUPLED. FOR RIGHT ANGLE THREADED ADAPTER
D-602-0126	CONTACT, PIN, COAX
D-602-0127	CONTACT, SOCKET, COAX
D-600-0030/0056	BRAID TERMINATOR
D-600-0019	STRAIN RELIEF
D-600-0601	RIGHT ANGLE ADAPTER TUBE

2.0 REFER TO RAYCHEM SPECIFICATION D-6025 FOR PERFORMANCE AND QUALIFICATION REQUIREMENTS. QUALIFICATION PENDING.

2.1 PERFORMANCE IS DEPENDENT UPON CORRECT USAGE OF SUITABLE AEROBIC ADHESIVE UPON ADAPTER THREADS. (LOCTITE TYPE 242 IS A SUITABLE ADHESIVE.)

3.0 TERMINATION PROCEDURE: RAYCHEM ES 61249.

4.0 USAGE: CONNECTORS ASSEMBLED FROM THESE KITS CAN HAVE THE CABLE DRESSED IN ANY ORIENTATION AROUND THE AXIS OF THE CONNETOR, CABLE SHOULD BE SECURED IN DESIRED ORIENTATION.

If this document is printed it becomes uncontrolled.
Check with the web for latest revision.

CAD NAME: 004951-2.DWG	DRAWN	J.B.K.	90 AUG 8	SIZE A	CODE IDENT. NO. 06090	DWG. NO. DK-621-X4XXR[-XX]	REV D
	ISSUED			DO NOT SCALE THIS DRAWING		SHEET 2 OF 2	