

P	LTR	DESCRIPTION	DATE FECHA	DWN DIBUJO	APVD APROBO
	Q	RELEASED	2/8/93	B.A.	B.A.
	A	REDRAWN & ADD DIMENSIONS	2/8/93	B.A.	B.A.
	B	ADD DIM & SCREW SPECIFICATION	2/8/96	ACH	ACH
	C	LM00 - 0009 - 97	27/1/97	ACH	ACH
	D	LM00 - 0110 - 97	14/5/97	ACH	ACH
	E	0G3A-0577-02	19/09/02	JR	ND

NOTES:



PART NUMBER	DESCRIPTION
157423-1	Binding Head .340dia #10-32 .312 long. Brass Screw (Electrical Type)
157423-2	Binding Head .340dia #10-32 .312 long. Brass Screw (Electrical Type) Bright Nickel Finish



CUTOFF MAX. ALLOWED 0.015

3




TORQUE OF 2-8 LB-IN ON SETTING OF SCREW

4

THREADS DEFORMED SO AS NOT TO ALLOW REMOVAL
OF THE SCREW

5

PART TO BE CLEAN AND OIL FREE



2	157423-2	SCREW (NICKEL PLATED)	1			NONE
2	157423-1	SCREW	1			NONE
1	157422-1	TAB FASTON .250 8 .187S.	1	1	BRASS 100-86	0.032+-0.001 082
ITEM	PART NUMBER	DESCRIPTION	-1	-2	MATERIAL	DIMENSIONS
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. ESTE PLANO ES UN DOCUMENTO CONTROLADO POR AMP INCORPORATED. ESTA SUJETO A CAMBIOS Y HAY QUE CONTACTAR AL DEPT. DE INGENIERIA POR LA ULTIMA REVISION.		DWN/DIBUJO A. CHAVEZ 08/26/96	AMP de Mexico S.A. Tlalnepantla, Mexico.			
DIMENSIONS: MEDIDAS, IN.		CHK/CONTROL A. CHAVEZ 08/26/96	NAME NOMBRE			
TOLERANCES UNLESS OTHERWISE SPECIFIED TOLERANCIAS SALVO OTRA INDICACION, 1 PLC/LUG $\pm$ 2 PLC/LUG $\pm$ 3 PLC/LUG $\pm 0.015'$ 4 PLC/LUG $\pm$ ANGLES/ANGULOS $\pm 1^\circ$		APVD/APROBO A. CHAVEZ 08/26/96	FASTON TAB ASSY			
MATERIAL		FINISH ACABADO	PRODUCT SPEC ESPEC. DE PRODUCTO	APPLICATION SPEC ESPEC. DE APLICACION	SIZE TAMANO	CAGE CODE CODIGO DE CELDA
			WEIGHT PESO		DRAWING NO PLANO NO	157431
					SCALE ESCALA NTS	SHEET HOJA 1 OF DE 1
						REV E