




Pin#	Name
1	DAT2
2	CD/DAT3
3	CMD
4	V _{DD1}
5	CLK
6	V _{SS}
7	DATORCLK+
8	DAT1RCLK-
9	V _{DD2}
10	V _{SS}
11	DO+
12	DO-
13	V _{SS}
14	D1-
15	D1+
16	V _{SS}
17	SWIO



	WITHOUT CARD	CARD MATED
DETECTION SW		

11	COIL SPRING	1	STAINLESS (Φ0.2)	-		
10	CAM FOLLOWER	1	STAINLESS (Φ0.3)	-		
9	LOCK	1	STAINLESS (t0.2)	-		
8	EJECT BAR	1	PA9T	-		COLOR:BLACK
7	Vdd2SW2 (+)	1	COPPER ALLOY (t0.1)	Contact: Au (0.3 μm UP) over Ni (1 μm UP) Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
6	Vdd2SW1	1	COPPER ALLOY (t0.12)	Contact: Au (0.3 μm UP) over Ni (1 μm UP) Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
5	DETECTION SW2	1	COPPER ALLOY (t0.1)	Contact: Au (0.3 μm UP) over Ni (1 μm UP) Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
4	DETECTION SW1 (GND)	1	COPPER ALLOY (t0.12)	Contact: Au (0.3 μm UP) over Ni (1 μm UP) Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
3	COVER FRAME	1	STAINLESS (t0.15)	Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
2	HOUSING	1	LCP	-		COLOR:BLACK
1	CONTACT	1	COPPER ALLOY (t0.1)	Contact: Au (0.5 μm UP) over Ni (2 μm UP) Terminal: Au (0.03 μm UP) over Ni (1 μm UP)		
符号	名 称 DESCRIPTION	個 数 QTY	材 料 MATERIAL	仕 工 FINISH		備 考 REMARKS

仕様書 (SPECIFICATION)		第1版 (ORIGINAL DATE) 28/FEB/2017		尺度 (SCALE) 5:1		シリーズ (SERIES) ST50		日本航空電子工業株式会社	
JACS-11173* JAHL-11173*		製図 DR.		名称 (TITLE) ST50S017VCA		 JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.		図面番号 (DRAWING NO.) SJ117915	
一般公差 (GENERAL TOLERANCE)		担当 CHK. K. KUME							
寸法 (DIMENSION)		査閲 APPD.							
±0.8		×° ±		承認 APPD. M. SHIMADA					
× ±0.4		×°×' ±							
×× ±0.1									
××× ±		単位 (UNIT) : mm		質量 (MASS)					

WISDOM承認 2017/03/07

JAЕ Connector DIV. Proprietary. Copyright(C) 2017, Japan Aviation Electronics Industry, LTD.