


OIL TIGHT Miniature Neon Indicators

FOR MOUNTING IN 11/16" CLEARANCE HOLE

When connecting a Neon Light to a circuit having one side grounded, always connect the hot side of the circuit to the terminal marked + (center contact).



T-3 1/4
B1A (NE-51)
B2A (NE-51H)
MINIATURE BAYONET BASE

See lamp ratings
on page L.

Recognized under the component
program of Underwriters'
Laboratories Inc.



MATERIALS AND FINISHES


- **Mounting Bushing:** Brass, white nickel finish. Optional, black nickel finish.
- **Lens Holder:** Brass, satin chrome finish. Optional, polished chrome or black nickel finish.
- **Internal-tooth-Lockwasher:** Phosphor bronze, white nickel finish.
- **Mounting Nut:** Brass, white nickel finish.

How to designate the three digit part number suffix (-XXX)

("Resistor" designations are given for B1A (NE-51) and B2A (NE-51H) Lamps.

FINISH	RESISTOR	HARDWARE
-2 black nickel	1-22K	3-water-tight,
-3 polished chrome	3-33K	oil tight on
-4 satin chrome	4-56K	the face of
	6-68K	the panel
	7-100K	

Note: The part numbers given in this catalog indicate standard indicator lights. The above table provides the standard and optional designations for Finish and Resistor where appropriate.



123-5863-1231-463
Dome lens

123 SERIES

screw terminals	soldering terminals	quick connect terminals
1/16 PANEL REF. "O" RINGS 5/64 X 7/8 O.D. FLANGE. PROJECTION BACK OF PANEL 1-3/8 MAX. SIGN MARKED ON THE TERMINAL CONNECTED TO THE CENTER CONTACT. 4-36 NS THD. 11/16-27 NS THD. MOUNTING BUSHING. 3/32 X 13/16 ACROSS FLATS HEX. NUT. INTERNAL TOOTH LOCKWASHER 1/30 ± .005 X 61/64 ± .010 O.D.	5/64 X 1/8 (2 SLOTS)	1/16 DIA. (2 HOLES)

BASE PART NUMBERS

105-125V AC-DC
110-125VAC
210-250V AC-DC

B1A
B2A
B2A

123-1308-12-143
123-1363-12-113
123-9363-12-163

123-0408-12-143
123-0463-12-113
123-9463-12-163


123-5708-12-143
123-5763-12-113
123-5863-12-163

CAP PART NUMBERS

VOLTAGES

LAMP

COMPLETE ASSEMBLY PART NUMBERS



DOME

123-1231-403
unfrosted

105-125V AC-DC
110-125VAC
210-250V AC-DC

B1A
B2A
B2A

123-1308-1231-443
123-1363-1231-413
123-9363-1231-463

123-0408-1231-443
123-0463-1231-413
123-9463-1231-463

123-5708-1231-443
123-5763-1231-413
123-5863-1231-463

Part numbers listed in this catalog designate products with RED lens. For ordering lens colors other than red, consult chart on page 1E.