





2		1					
LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	05OCT2001	EZ	DB




796682-3 AS SHOWN



130	25	2-796682-5
120	24	2-796682-4
115	23	2-796682-3
110	22	2-796682-2
105	21	2-796682-1
100	20	2-796682-0
95	19	1-796682-9
90	18	1-796682-8
85	17	1-796682-7
80	16	1-796682-6
75	15	1-796682-5
70	14	1-796682-4
65	13	1-796682-3
60	12	1-796682-2
55	11	1-796682-1
50	10	1-796682-0
45	9	796682-9
40	8	796682-8
35	7	796682-7
30	6	796682-6
25	5	796682-5
20	4	796682-4
15	3	796682-3
10	2	796682-2
DIM. A	Nº OF POS.	PART NUMBER

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.3

1 PLC ±.3

2 PLC ±.25

3 PLC ±.

4 PLC ±.

ANGLES ±2

MATERIAL

FINISH

DWN 05APR2001
E. ZANOLINI

CHK 05APR2001
D. BIEVENOUR

APVD 05APR2001
D. BIEVENOUR

PRODUCT SPEC
108-20166

APPLICATION SPEC
114-20079

WEIGHT
-

CUSTOMER DRAWING

BUCHANAN Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TERMINAL BLOCK PCB MOUNT,
SIDE ENTRY WIRE, STACKING
W/ INTERLOCK, 5mm PITCH.

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-796682

RESTRICTED TO
-

SCALE
3:1

SHEET
1

OF
2

REV
A

4

3

2

1

LOC	DIST	REVISIONS					
FT	0	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0.
COLOR: BLACK
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

- 2
- SUITABLE FOR 1,6-2,4mm. PCB THICKNESS.
- 3
- END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4
- WIRE SIZE RANGE
SOLID WIRE: 0,03-2,5mm (13AWG)
STRANDED WIRE: 0,03-1,5mm (15AWG)
- 5
- RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 6
- IMO CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.



NOT CUMULATIVE TOLERANCE.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH

-

DWN
E. ZANOLINI
05APR2001

CHK
D. BIEVENOUR
05APR2001

APVD
D. BIEVENOUR
05APR2001

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608

NAME
TERMINAL BLOCK PCB MOUNT,
SIDE ENTRY WIRE, STACKING
W/ INTERLOCK, 5mm PITCH.

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-796682

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
-

SHEET
2

OF
2

REV
A

AMP 1470-19 REV 31MAR2000