


REV		REVISIONS			
NC		SYM	DESCRIPTION	DATE	APPROVED
DT06-08S*-P004		NC	REDRAWN / REPLACES PREVIOUS		
			REVISED PER E.O. P19638	10-12-07	RDR




5. MATERIAL: SHELL: PLASTIC; SEAL: RUBBER
4. THIS PLUG MATES WITH THE DTO4-08P*-**** RECEPTACLE (* = A,B,C,D KEYS; **** = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.
3. FOR CONTACTS AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000 AND 0425-017-0000.
2. DIMENSIONS ARE $\pm .025$ [0.63] UNLESS OTHERWISE SPECIFIED.
1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
- NOTES:

CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	WIRE RANGE [mm ²] REF. ONLY
16	.088 [2.24]	.145 [3.68]	14-20 AWG [2.0-0.5]


SIGNATURE & DATE		8 WAY PLUG -P004 MOD. DT SERIES		EP	MATL. CODE
DR	A. MALAGON 11SEP07	ENVELOPE		3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	<i>[Signature]</i> 10/12/07				
PE	<i>[Signature]</i> 10/12/07				
APPD	<i>[Signature]</i> 10-12-07				
SCALE	NONE	WT		B DT06-08S*-P004 DWG SIZE CODE 11139 SHEET 1 OF 2	

REV	DT06-08S*-P004	REVISIONS			
NC		SYM	DESCRIPTION	DATE	APPROVED
		NC	SEE SHEET #1	10-12-07	ROR


PART NO.
DT06-08SA-P004
KEY ARRANGMENT -A-
COLOR: GRAY




PART NO.
DT06-08SB-P004
KEY ARRANGMENT -B-
COLOR: BLACK



PART NO.
DT06-08SC-P004
KEY ARRANGMENT -C-
COLOR: GREEN



PART NO.
DT06-08SD-P004
KEY ARRANGMENT -D-
COLOR: BROWN



NOTES:

SIGNATURE & DATE		8 WAY PLUG -P004 MOD. DT SERIES		EP	MATL. CODE
DR	A. MALAGON 11SEP07			 3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	<i>[Signature]</i> 10/12/07				
PE	<i>[Signature]</i> 9/14/07			B DT06-08S*-P004	
APPD	<i>[Signature]</i> 10-10-07	ENVELOPE		DWG SIZE	CODE 11139
SCALE	NONE			SHEET 2 OF 2	