

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, — .

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REVISED PER ECO-10-013614		13OCT10	HMR	CR

MATERIAL:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: BRIGHT TIN OVER COPPER ALLOY.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.


ELECTRICAL:
RATED CURRENT UL/CSA:
CLASS C: 20A, 300V.
CLASS D: 5A, 600V.
WIRE RANGE: 12-22 AWG.

MECHANICAL:
RECOMMENDED TORQUE: 7 IN-LB.
OPERATING TEMP.: 105°C MAX.

1 STAINLESS STEEL SCREWS.



9.000	9.314	23	JC6-P207-23	7-796985-8
8.625	8.939	22	JC6-P207-22	7-796985-7
8.250	8.564	21	JC6-P207-21	7-796985-6
7.875	8.189	20	JC6-P207-20	5-1437666-8
7.500	7.814	19	JC6-P207-19-253	9-796985-5
7.500	7.814	19	JC6-P207-19	7-796985-5
7.125	7.439	18	JC6-P207-18-252	9-796985-4
7.125	7.439	18	JC6-P207-18	7-796985-4
6.750	7.064	17	JC6-P207-17	7-796985-3
6.375	6.689	16	JC6-P207-16	7-796985-2
6.000	6.314	15	JC6-P207-15	7-796985-1
5.625	5.939	14	JC6-P207-14	7-796985-0
5.250	5.564	13	JC6-P207-13	6-796985-9
4.875	5.189	12	JC6-P207-12-251	9-796985-3
4.875	5.189	12	JC6-P207-12	6-796985-8
4.500	4.814	11	JC6-P207-11	6-796985-7
4.125	4.439	10	JC6-P207-10-250	9-796985-2
4.125	4.439	10	JC6-P207-10	4-1437665-0
3.750	4.064	9	JC6-P207-09	3-1437665-9
3.375	3.689	8	JC6-P207-08	3-1437665-8
3.000	3.314	7	JC6-P207-07-249	9-796985-1
3.000	3.314	7	JC6-P207-07	6-796985-6
2.625	2.939	6	JC6-P207-06	3-1437665-7
2.250	2.564	5	JC6-P207-05	3-1437665-6
1.875	2.189	4	JC6-P207-04-248	9-796985-0
1.875	2.189	4	JC6-P207-04	3-1437665-5
1.500	1.814	3	JC6-P207-03	3-1437665-4
1.125	1.439	2	JC6-P207-02	3-1437665-3
DIM B	DIM A	NO OF POS	CATALOG NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 9/15/03	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608				
DIMENSIONS: INCHES		CHK S. YODER 9/15/03	NAME JC6-P207-XX ASSEMBLY				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .01 3 PLC ± .005 4 PLC ± - ANGLES ± -	APVD S. YODER 9/15/03					
		PRODUCT SPEC —					
		APPLICATION SPEC —					
MATERIAL —		FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-3-1437665-3	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV D		