




PART NUMBER	PLUG FINGER	HANDLE	HANDLE CABLE OPENING I.D.
35HDRABAU	GOLD	BLACK	0.29
35HDRABAUS	GOLD	BLACK	0.175
35HDRANAU	GOLD	NICKEL	0.29
35HDRANAUS	GOLD	NICKEL	0.175
35HDRANN	NICKEL	NICKEL	0.29
35HDRANNS	NICKEL	NICKEL	0.175

MATERIALS:

PLUG MOLDING COMPOUND - L.C.P. BLACK	
SLEEVE, PLUG BODY	- BRASS, NICKEL OR GOLD PLATED
RING SLEEVE	- BRASS, NICKEL OR GOLD PLATED
TIP ROD	- BRASS, NICKEL OR GOLD PLATED
HOUSING	- ZINC, BLACK OR NICKEL PLATED
TUBULAR INSULATOR	- MYLAR, TRANSLUCENT
HANDLE	- BRASS, BLACK OR NICKEL PLATED
CLAMP TERMINAL	- CRS, TIN PLATED
SOLDER LUGS (TIP & RING)	- BRASS, TIN PLATED



TUBULAR INSULATOR
SHIPPED UNASSEMBLED

HANDLE
SHIPPED UNASSEMBLED

CABLE OPENING I.D.
SEE TABLE

CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS	SIZE	WIDTH	MULT	LBS/M	TEMPER			
						FINISH			MATERIAL				
						SPEC No.			SPEC No.				
						FIRST USED ON		SCALE		Switchcraft®			
						DATE DRAWN		BY	CHKD				APVD
A	24662	3-23-04	JL	AKE			6-27-00	AKE	AKE	AKE			
									3-23-04	3-23-04	SHEET 1 OF 1		
REV	ECO NUMBER	DATE	BY	APVD			NAME			PART No.			REV
REVISIONS					DO NOT SCALE DRAWING	3.5mm RA STEREO PLUG			35HDRA SERIES			A	