

A	B	C	D	E																																																		
		REV.	DESCRIPTION	ECN NO.	NAME	DATE																																																
		SPECIFICATIONS		<table border="1"> <thead> <tr> <th>P/N</th> <th>PIN</th> <th>DIM.A</th> <th>DIM.B</th> </tr> </thead> <tbody> <tr><td>B200UP-ZD01P-PC028</td><td>1</td><td>0.00</td><td>2.00</td></tr> <tr><td>B200UP-ZD02P-PC028</td><td>2</td><td>2.00</td><td>4.00</td></tr> <tr><td>B200UP-ZD03P-PC028</td><td>3</td><td>4.00</td><td>6.00</td></tr> <tr><td>B200UP-ZD04P-PC028</td><td>4</td><td>6.00</td><td>8.00</td></tr> <tr><td>B200UP-ZD05P-PC028</td><td>5</td><td>8.00</td><td>10.00</td></tr> <tr><td>B200UP-ZD06P-PC028</td><td>6</td><td>10.00</td><td>12.00</td></tr> <tr><td>B200UP-ZD07P-PC028</td><td>7</td><td>12.00</td><td>14.00</td></tr> <tr><td>B200UP-ZD08P-PC028</td><td>8</td><td>14.00</td><td>16.00</td></tr> <tr><td>B200UP-ZD09P-PC028</td><td>9</td><td>16.00</td><td>18.00</td></tr> <tr><td>.....</td><td>....</td><td>....</td><td>....</td></tr> <tr><td>B200UP-ZD40P-PC028</td><td>40</td><td>(PIN-1)x2.0</td><td>(PIN)x2.0</td></tr> </tbody> </table>			P/N	PIN	DIM.A	DIM.B	B200UP-ZD01P-PC028	1	0.00	2.00	B200UP-ZD02P-PC028	2	2.00	4.00	B200UP-ZD03P-PC028	3	4.00	6.00	B200UP-ZD04P-PC028	4	6.00	8.00	B200UP-ZD05P-PC028	5	8.00	10.00	B200UP-ZD06P-PC028	6	10.00	12.00	B200UP-ZD07P-PC028	7	12.00	14.00	B200UP-ZD08P-PC028	8	14.00	16.00	B200UP-ZD09P-PC028	9	16.00	18.00	B200UP-ZD40P-PC028	40	(PIN-1)x2.0	(PIN)x2.0
P/N	PIN	DIM.A	DIM.B																																																			
B200UP-ZD01P-PC028	1	0.00	2.00																																																			
B200UP-ZD02P-PC028	2	2.00	4.00																																																			
B200UP-ZD03P-PC028	3	4.00	6.00																																																			
B200UP-ZD04P-PC028	4	6.00	8.00																																																			
B200UP-ZD05P-PC028	5	8.00	10.00																																																			
B200UP-ZD06P-PC028	6	10.00	12.00																																																			
B200UP-ZD07P-PC028	7	12.00	14.00																																																			
B200UP-ZD08P-PC028	8	14.00	16.00																																																			
B200UP-ZD09P-PC028	9	16.00	18.00																																																			
.....																																																			
B200UP-ZD40P-PC028	40	(PIN-1)x2.0	(PIN)x2.0																																																			
		GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD																																																			
RECOMMEND P.C.B LAYOUT	PCB TOLERANCE:±0.05 (TOP VIEW)	DIM. TOL. x ±0.30 x.x ±0.20 x.xx ±0.10	TITLE: 2.0FH H4.3 1xnPin 180度 W2.4 U型 PC2.8 6T																																																			
	GENERAL ANGLE: X ±5° X.X ±1° X.XX ±0.5°	DWG. NO.: B200UP-ZDXP-PC028			CHECKED: MAX																																																	
		PART NO.: B200UP-ZDXP-PC028			DRAWN: ELLA																																																	
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4		LAYER: bxconn																																															



BXCONN