




| REV. | ECN NO. | DESCRIPTION | DESIGN | APPROVAL | DATE       |
|------|---------|-------------|--------|----------|------------|
| A1   | NEW     | 新版发行        |        |          | 2025.09.23 |

- 技术要求:
- 1.打铜底0.5-1μm,镍2-2.5μm, 镀雾锡3-5μm。
  - 2.铆好后不得有松动现象。
  - 3.插脚尖部符合可焊性要求。
  - 4.螺纹需符合通止规/止针要求。
  - 5.螺纹扭矩：1.8Nm.
  - 6.额定电流：150A.

|                                                                                                                                                                            |        |                                  |  |                        |  |       |                                                                                       |     |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|----------------------------------|--|------------------------|--|-------|---------------------------------------------------------------------------------------|-----|
| >30.±0.4                                                                                                                                                                   | X.°±   | PART NO:<br>TT56120177-1525      |  | XFCN 兴飞连接器             |  |       |                                                                                       |     |
| 6-30±0.3                                                                                                                                                                   | .X°±   |                                  |  |                        |  |       |                                                                                       |     |
| 0-6±0.2                                                                                                                                                                    | .XX°±  | TITLE:<br>PCB SOLDERING TERMINAL |  | 0769-82001899          |  |       |                                                                                       |     |
| ANGLES±1°                                                                                                                                                                  | .XXX°± |                                  |  | www.xfconn.com         |  |       |                                                                                       |     |
| UNITS:                                                                                                                                                                     | mm     | APPD<br>Chen ZhiQiang            |  | DWG NO:<br>/           |  |       |                                                                                       |     |
| THESE DRAWINGS AND SPECIFICATIONS<br>ARE THE PROPERTY OF XFCN AND SHALL<br>NOT BE REPRODUCED, COPIED OR CUED IN<br>ANY MANNER WITHOUT THE PRIOR<br>WRITTEN CONSENT OF XFCN |        |                                  |  | CHKD<br>Liu Wei        |  | VIEW  |  |     |
|                                                                                                                                                                            |        |                                  |  | DRAW<br>Chen HongJiang |  | SCALE | SHEET                                                                                 | REV |
|                                                                                                                                                                            |        |                                  |  | DATE<br>2025.09.23     |  | NONE  | 1/1                                                                                   | A1  |

|    |    |      |          |    |
|----|----|------|----------|----|
| 2  | 垫片 |      | SPCC     | 1  |
| 1  | 插脚 |      | H62 (Y2) | 1  |
| 序号 | 名称 | 零件编号 | 材质       | 数量 |