

[illegible][illegible]

A0

REV

DATE

MODIFICATION DESCRIPTION

CHANGE

OPERATION
X.X ±0.30
X.XX ±0.20
X.XXX ±0.10
Angle ±3°
DIM TOL

DRAW

CHECK

APPROVE

SCALE
UNIT mm
SIZE A4
SHEET 1/1
PROJ.

FIT
mm
A4
1/1

PART NO.
TITLE:

1130300164
HY-NAWR

RoHS

①

②

③

0.5±0.03(SQ)

2.00±0.15(PITCH)

DIMA±0.2
DIMB±0.15
DIMC±0.2

2.60±0.2

2 PIN 结构样式
(Structural style)

3 PIN 结构样式
(Structural style)

适用线路板(PCB LAYOUT)
DIMA±0.1
2±0.05
1.2±0.1
3.80
3.85±0.1
3.70
1.20
2.2
CONN.

技术指标(Technical Index):
1.温度范围(Temperature range):-40°C~+ 105 ° C。
2.额定电压(Rated voltage): 200V, AC。
3.额定电流(Rated Current):2A AC/DC
4.接触电阻(Contact resistance): ≤20mΩ
5.绝缘电阻(Insulation resistance): ≥1000MΩ。
6.产品料号(Product material No.):

CTK	DIM A	DIM B	DIM C
2	2.00	4.90	8.00
3	4.00	6.90	10.00
4	6.00	8.90	12.00
5	8.00	10.90	14.00
6	10.00	12.90	16.00
7	12.00	14.90	18.00
8	14.00	16.90	20.00
9	16.00	18.90	22.00
10	18.00	20.90	24.00
11	20.00	22.90	26.00
12	22.00	24.90	28.00
13	24.00	26.90	30.00
14	26.00	28.90	32.00
15	28.00	30.90	34.00
16	30.00	32.90	36.00
17	32.00	34.90	38.00
18	34.00	36.90	40.00
19	36.00	38.90	42.00
20	38.00	40.90	44.00

- [illegible]

[illegible]

RoHS		2	3	4	5	6	7	8	9												
								<table><tr><th>序号 (NO.)</th><th>品名 (Name)</th><th>材质 (Material)</th></tr><tr><td>①</td><td>2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)</td><td>LCP UL94V-0 本色 Natural</td></tr><tr><td>②</td><td>2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr><tr><td>③</td><td>2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)</td><td>铜合金/表面镀锡 Copper Alloy/ Tin Plating</td></tr></table>		序号 (NO.)	品名 (Name)	材质 (Material)	①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural	②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating	③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
序号 (NO.)	品名 (Name)	材质 (Material)																			
①	2.00 F型卧式2代WTB胶芯 2.00 Pitch R/A Wire To Board Housing(H=5.2)	LCP UL94V-0 本色 Natural																			
②	2.00 F型卧式2代WTB端子 2.00 Pitch R/A Wire To Board Terminal(H=5.2)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																			
③	2.00 F型卧式WTB焊片 2.00 Pitch R/A Wire To Board Fitting Nail(H=5.6)	铜合金/表面镀锡 Copper Alloy/ Tin Plating																			