



ISO9001-2015
Certificate No.672Q22020207194

No.T52210311961TC Date;OCT 12,2022 No.T52310270397TC Date:apr 15.2023

承認書

SPECIFICATION FOR APPROVAL

客户名稱
CUSTOMER

品名規格
DESCRIPTION RH3.5x6x0.8x2

客户料號
CUS. P/N

提出日期
DATE 2025.05.12

出 圖 RDAWING		
發 行 MADE	復 核 CHECKED	確 認 APPROVED
李光赫	方煜镠	梁琼
销售部：张 丽		

承 認 CUSTOMER APPROVE




深圳市航宇磁电有限公司

SPECIFICATION 產品規格書		DRAWING NO.: CK-RH3.5-6-0.8	
CUSTOMER			
CUSTOMER TYPE			
ITEM		RH3. 5×6×0. 8×2	
MATERIAL		CKA	
CUSTOMER P/N			
SCALE:	UNIT:	METHOD:	DATE:
NONE	mm.	第三角法	
DRAWN/DATE	CHECK/DATE	APPROVED/DATE	ISSUE NO
李光赫	方煜镗	梁琼	

1. DIMENSIONS:

ϕA	ϕB	C	D
3.50±0.15	6.00±0.30	28.00±0.30	5.0±1.0



深圳市航宇磁电有限公司

2. ELECTRONIC CHARACTERISTICS:

ITEM.	IMPEDANCE(Ω)
	100MHz
SPEC.	170 Ω MIN

3.NOTES:

(1) WIRE & WINDING: ϕ CP0.6

(2) TEST FREQUENCY: 100MHZ.

(3) TEST METER: HP-4191A RF.

TEST DATA

ITEM.	ϕ A	ϕ B	C	D		
SPEC.	3.50±0.15	9.00±0.30	28.00±0.30	5.0±1.0		
01.	3.63	6.01	28.1	4.6		
02.	3.58	6.08	28.2	4.6		
03.	3.54	6.05	28.1	4.6		
04.	3.70	6.10	28.2	4.7		
05.	3.68	6.08	28.2	4.7		
06	3.75	6.96	28.1	4.8		
07	3.70	6.95	28.1	4.5		
08	3.73	6.93	28.2	4.4		
09	3.57	6.10	28.2	4.6		
10	3.66	6.17	28.2	4.7		
ITEM.	IMPEDANC E(Ω)					
	100MHz					
SPEC.	170 Ω MIN					
1	198.86					
2	195.33					
3	202.88					
4	212.45					
5	210.23					
6	216.83					
7	205.65					
8	198.75					
9	206.36					
10	208.45					