


Features

- Used with threaded fasteners (for example a bolt and a nut)
- Designed to increase the area of load distribution
- Larger outer diameter makes this washer ideal for spreading tightening forces over a greater area than a conventional washer, as well as over-sized holes
- Manufactured from A2 stainless steel, they are ideal for external - as well as internal use, offering fantastic resistance against corrosion

RS PRO Stainless-Steel Washers

RS Stock No.: 526805,526827,526833,526849
,530090,530107,530113,276803,276819
,1933451,6604623,5072735,6604627,5072678,
5072684,5072690,5072713,5072729,1933483
,1933484



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Used with threaded fasteners (for example, a bolt or a nut), they are designed to increase the area of load distribution. When the threaded fastener is tightened, there is a risk of the surface becoming stressed. A washer helps spread the tightening forces applied over an even and increased area, reducing the risk of surface stress and damage. Having an exaggerated outer diameter, mudguard washers are ideal for spreading out the tightening forces over a wider surface area, as well as over-sized holes. Manufactured from A2 stainless steel, they are ideal for external - as well as internal use, offering fantastic resistance against corrosion.

General Specifications

d1	M4 x 20	M4 x 25	M5 x 20	M5 x 25	M5 x 30	M6 x 20	M6 x 25	M6 x 30	M6 x 40	M8 x 20	M8 x 25	M8 x 30
d2 max.	20	25	20	25	30	20	25	30	40	20	25	30
s nom.	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
d1	M8 x 35	M8 x 40	M8 x 50	M10 x 25	M10 x 30	M10 x 35	M10 x 40	M10 x 50	M12 x 30	M12 x 35	M12 x 40	M12 x 50
d2 max.	35	40	50	25	30	35	40	50	30	35	40	50
s nom.	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5

Similar Products

Stock No.	Brand
6604623	M4 X 20
5072735	M4 X 25
2874008	M5 X 20
6604627	M5 X 25
2873873	M5 X 30
2873875	M6 X 20
2874006	M6 X 25
5072678	M6 X 30
2873876	M6 X 40
2874007	M8 X 20
5072684	M8 X 25
5072690	M8 X 30

2873878	M8 X 35
5072713	M8 X 40
2874009	M8 X 50
5072729	M10 X 25
2874010	M10 X 30
2874012	M10 X 35
2873880	M10 X 40
2873874	M10 X 50
2873877	M12 X 30
2873879	M12 X 35
1933483	M12 X 40
1933484	M12 X 50

