

## Features

- A set of 3 adjustable wrenches made from high performance alloy steel and developed to focus on innovation and ergonomics measurement
- The jaw does not fall out even at maximum opening of the wrench

## RS PRO Adjustable Wrench Set 160mm, 210mm, 260mm Length

RS Stock No.: 2821248



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- *RS PRO Adjustable Spanner*
- *This adjustable spanner is precision hardened for excellent quality and a long and reliable service life. Constructed from chrome vanadium steel with a black phosphate finish. The adjustable wrench's anti-corrosion coating means it is suitable for use in challenging environments.*
- *The spanner features a common thumb-adjustable screw for quick and precise adjustment of the jaw width.*

## General Specifications

Wrench Type	Adjustable Wrench
Material	Chrome Vanadium Steel
Overall length	160mm, 210mm, 260mm
Handle Type	Plastic
Jaw Capacity	24mm, 30mm, 34mm
Number of Piece	3

## Mechanical Specifications

Finished	Black Phosphate
Scale in Jaw	mm /Metric
Product weight	154gram, 276gram, 485gram
Pouch Bag	Include

## Approvals

Declarations	ROHS DOC
Standards Met	DIN 3117 (Torque, Hardness and Gauges)

## Similar Products

Stock No.	Brand	Product Name	Attribute 1	Attribute 2	Attribute 3
2821238	RS PRO	Adjustable Spanner	160mm Overall	24mm Jaw	Plastic Handle
2821239	RS PRO	Adjustable Spanner	210mm Overall	30mm Jaw	Plastic Handle
2821241	RS PRO	Adjustable Spanner	310mm Overall	41mm Jaw	Plastic Handle
2821248	RS PRO	Adjustable Spanner Set	160/210/260mm Overall	24/30/34mm Jaw	Plastic Handle
2821242	RS PRO	Adjustable Spanner	215mm Overall	39mm Jaw	Plastic Handle
2821245	RS PRO	Adjustable Spanner	255mm Overall	50mm Jaw	Plastic Handle
2821246	RS PRO	Adjustable Spanner	308mm Overall	60mm Jaw	Plastic Handle
2821243	RS PRO	Adjustable Spanner	214mm Overall	39mm Jaw/ Extra thin jaw	Plastic Handle
2821236	RS PRO	Adjustable Spanner	115mm Overall	14.5mm Jaw	Metal Handle
2821237	RS PRO	Adjustable Spanner	207mm Overall	29mm Jaw	Metal Handle
2821244	RS PRO	Adjustable Spanner	200mm Overall	40mm Jaw/ Reversible pipe use	Bi-Materials Handle
2821240	RS PRO	Adjustable Spanner	257mm Overall	52mm Jaw/ Reversible pipe use	Bi-Materials Handle