

## Features

- Suitable for liquid fuels
- Reduced effort application through the recessed grip
- No rusty splits in the fuel
- Less water condensate in the jerry can
- Integral discharge spout to be stored in the jerry can complete with patented jerry can locking cap
- No contamination of the discharge spout when storing the jerry can in a vehicle
- Dimensions compatible with military jerrycans
- Lower conductivity of temperature in comparison to metal version
- Robust and resistant against impact
- UN-approval

## RS PRO HDPE Fuel Can, 5L

RS Stock No.: 703-1095



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*Use this bright red fuel can to transport fuel safely and conveniently. It has a capacity of 5 litres and is easy to carry thanks to its moulded handle. There's a separate, flexible spout that can be stored inside it.*

*At 20 mm, the can's discharge spout is relatively wide and has integrated ventilation to make pouring smoother and safer. Its cover cap comes conveniently attached with a flexible band, so it won't be misplaced. HDPE (high-density polyethylene) material makes the body of the fuel can lightweight – weighing just 0.64 kg.*

*Besides passing the rigorous testing necessary for all of our RS PRO products, the can has European safety certifications from German organisations BAM and TUV. It's ideal for refuelling vehicles, as well as for transporting and dispensing fluids in industrial or agricultural situation*

## Technical Data

Capacity (l)	5
UN approval	un 3H1/Y/150/.../CZ/PRES-IMET 1174
Material jerrycan	HDPE (high density polyethylene)
Colour of can	red, RAL 3001
Material jerrycan locking cap and adapter	polypropylene
Material discharge spout and fixation strap	LDPE (polyethylene of low density)
Colour jerrycan locking cap	red, RAL 3001
Colour fixation strap and adapter	steel-grey, RAL 7011
Colour discharge spout	white, transparent
Length of discharge tube (mm)	175
Diameter discharge spout outside (mm)	20
Height (mm)	237
Base LxB (mm)	331 x 185
Weight (kg)	0,64

## General Specifications

Flexible discharge spout with integral ventilation
Spout is stored inside jerrycan
Cover cap is secured against loss with flexible band
With EAN bar code

## Similar Products

Stock No.	Capacity	Colour of can	Material jerrycan	Length of discharge tube (mm)	Diameter discharge spout outside (mm)	Height (mm)	Base LxB (mm)	Weight (kg)
703-1095	5L	red, RAL 3001	HDPE	175	20	237	331 x 185	0,64
703-1098	10L	red, RAL 3001	HDPE	245	20	318	329 x 195	0,82
703-1092	20L	red, RAL 3001	HDPE	245	20	410	385 x 229	1,28