






REV	DESCRIPTION OF CHANGE	REVIEWED BY	ISSUE DATE
A	FIRST ISSUE	X.YAN	2021-08-01


- NOTES:
- 1.MATERIAL: NICKEL SILVER, THICKNESS 0.25mm
 - 2.PACKAGING: TRAY PACKAGING
 - 3.TEMPERATURE:
 OPERATION : -40°C TO +85°C
 STORAGE : -55°C TO +105°C




TITLE SFP 1X6 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd Web: http://www.cd-tek.com		
PART NO. SFP 747470001 1X6Y-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:1/4
			.XXX±0.10		REV:A




TITLE SFP 1X6 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd Web: http://www.cd-tek.com		
PART NO. SFP 747470001 1X6Y-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:2/4
			.XXX±0.10		REV:A




TITLE SFP 1X6 CAGE			CND-tek		深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd Web: http://www.cd-tek.com		
PART NO. SFP 747470001 1X6Y-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1"	SCALE: 1:1	SHEET:3/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5"			
			.XXX±0.10				




MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL



SECTION A-A



MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL



SECTION A-A

TITLE SFP 1X6 CAGE			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd Web: http://www.cd-tek.com		
PART NO. SFP 747470001 1X6Y-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:4/4
			.XXX±0.10		REV:A