





ROHS

REV.	ECN. #	DESCRIPTION	DATE
A0		NEW RELEASE	04/15/22



NOTES:

1. MATERIAL:

HOUSING: Polycarbonate Black UL94V-0

Terminal: Copper Alloy

Shell: Stainless Steel

2. Product should not shrink, dirty, deformation, leak of material

3. Products must comply with RoHS requirements

MILLIMETERS	INCH
L* ±2°	L* ±2°
.I ±0.30	.I ±0.012
.XX ±0.20	.XX ±0.008
.XXX ±0.10	.XXX ±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.




东莞市金比莱五金塑胶科技有限公司



DongGuan JinBiLai Metal Plastic Technology Co., Ltd

TITLE	1.3MM MICRO SMD TRAY	DR		
PART NO.	102314332-FS	CHKD		
PRO J.	PAGE 1/2	UNITS mm	APPD	
SIZE	A4	SCALE 1:1	DIS NO.	KT004-001<客户图>


ROHS



PRODUCT





TRAY





51PCS/Box



An empty plate on top



PE Bag



BOX



料号	品名规格	数量
303050006	Clapboard (Material B=8 T=7 210*210)	2PCS
303040087	Box (K=K,T=7.0,240*240*215)	1PCS
303060007	PE Bag (T=0.08mm , 400*500 , Opening400)	1PCS
303200019	Blister plate (100PCS/Plate)	51PCS
102314332-FS	Product	4000PCS

MILLIMETERS	INCH
X ° ±2°	X ° ±2°
.X ±0.20	.X ±0.012
.XX ±0.10	.XX ±0.008
.XXX±0.05	.XXX±0.004

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.



东莞市金比莱五金塑胶科技有限公司
DongGuan JinBiLai Metal Plastic Technology Co.,Ltd

TITLE	1.38H NANO SIM TRAY	DR		
PART NUM	102314332-FS	CHKD		
PROJ.	PAGE 2/2	UNITS mm	APPD	
SIZE	A4	SCALE 3:1		KT004-001<客户图>