





SECTION A-A




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围:  $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$ .
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻:  $\leq 0.02\Omega$ .
6. 绝缘电阻:  $\geq 100\text{M}\Omega$ .
7. 额定电流: 0.5A AC/DC.

| 序号 | 品名            | 材质                  |
|----|---------------|---------------------|
| 1  | 0.8-C型卧式WTB胶芯 | LCP<br>UL94 V-0 自然色 |
| 2  | 0.8-C型立式WTB端子 | 铜合金/表面镀锡            |
| 3  | 0.8-C型卧式WTB焊片 | 铜合金/表面镀锡            |

| Part No          | CKT | A     | B     |
|------------------|-----|-------|-------|
| ZX-0.8-2PWT-XM2  | 2   | 0.80  | 3.80  |
| ZX-0.8-3PWT-XM2  | 3   | 1.60  | 4.60  |
| ZX-0.8-4PWT-XM2  | 4   | 2.40  | 5.40  |
| ZX-0.8-5PWT-XM2  | 5   | 3.20  | 6.20  |
| ZX-0.8-6PWT-XM2  | 6   | 4.00  | 7.00  |
| ZX-0.8-7PWT-XM2  | 7   | 4.80  | 7.80  |
| ZX-0.8-8PWT-XM2  | 8   | 5.60  | 8.60  |
| ZX-0.8-9PWT-XM2  | 9   | 6.40  | 9.40  |
| ZX-0.8-10PWT-XM2 | 10  | 7.20  | 10.20 |
| ZX-0.8-11PWT-XM2 | 11  | 8.00  | 11.00 |
| ZX-0.8-12PWT-XM2 | 12  | 8.80  | 11.80 |
| ZX-0.8-13PWT-XM2 | 13  | 9.60  | 12.60 |
| ZX-0.8-14PWT-XM2 | 14  | 10.40 | 13.40 |
| ZX-0.8-15PWT-XM2 | 15  | 11.20 | 14.20 |

| Part No          | CKT | A     | B     |
|------------------|-----|-------|-------|
| ZX-0.8-16PWT-XM2 | 16  | 12.00 | 15.00 |
| ZX-0.8-17PWT-XM2 | 17  | 12.80 | 15.80 |
| ZX-0.8-18PWT-XM2 | 18  | 13.60 | 16.60 |
| ZX-0.8-19PWT-XM2 | 19  | 14.40 | 17.40 |
| ZX-0.8-20PWT-XM2 | 20  | 15.20 | 18.20 |
| ZX-0.8-21PWT-XM2 | 21  | 16.00 | 19.00 |
| ZX-0.8-22PWT-XM2 | 22  | 16.80 | 19.80 |
| ZX-0.8-23PWT-XM2 | 23  | 17.60 | 20.60 |
| ZX-0.8-24PWT-XM2 | 24  | 18.40 | 21.40 |
| ZX-0.8-25PWT-XM2 | 25  | 19.20 | 22.20 |
| ZX-0.8-26PWT-XM2 | 26  | 20.00 | 23.00 |
| ZX-0.8-27PWT-XM2 | 27  | 20.80 | 23.80 |
| ZX-0.8-28PWT-XM2 | 28  | 21.60 | 24.60 |



| 制图<br>DRAWN | 变更内容<br>DESCRIPTION | 日期<br>DATE | GENERAL TOLERANCE            | 制图<br>DRAWING  | ROSE |
|-------------|---------------------|------------|------------------------------|----------------|------|
|             |                     |            | X. $\pm 0.5$ $\pm 1^{\circ}$ | 审核<br>CHECK    | LEO  |
|             |                     |            | X.X $\pm 0.2$                | 核准<br>APPROVAL | JOHN |
|             |                     |            | X.XX $\pm 0.1$               | 单位<br>UNITS    | MM   |
|             |                     |            |                              | 比例<br>SCALE    | 1:1  |

|                                                                     |                    |             |     |
|---------------------------------------------------------------------|--------------------|-------------|-----|
| 料号<br>PART NO.                                                      | ZX-0.8-NPWT-XM2    | 版本<br>REV.  | A   |
| 品名<br>TITLE                                                         | 0.80 Pitch C型卧式WTB | 页次<br>SHEET | 1/1 |
| 客户料号<br>CUTM.NO.                                                    |                    |             |     |
| 兆星精密电子(深圳)有限公司<br>ShenZhen ZhaoXing Precision electronics Co., Ltd. |                    |             |     |