







MAPX	MODIFICATION	DATE	DRAW	APPROVE
	High photosynthesis 台高(H)	The female seat height 母座半高(H1)	The male seat height 公座半高(H2)	Insertion height (H3)
	4.0	3.0	1.0	1.9
	4.5	3.5	1.0	1.9
	5.0	3.0/4.0	2.0/1.0	1.9
	5.5	3.5/4.5	2.0/1.0	1.9
	6.0	4.0	2.0	1.9
	6.5	4.5	2.0	1.9
	7.0	3.0	4.0	1.9
	7.5	3.5	4.0	1.9
	8.0	4.0	4.0	1.9
	8.5	4.5	4.0	1.9



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

Part No	CKT	A	B	C	D	E
BTB0.830-8PLBSB1-MB42	8	2.40	3.50	5.10	4.20	4.00
BTB0.830-10PLBSB1-MB42	10	3.20	4.30	5.90	5.00	
BTB0.830-12PLBSB1-MB42	12	4.00	5.10	6.70	5.80	
BTB0.830-14PLBSB1-MB42	14	4.80	5.90	7.50	6.60	
BTB0.830-16PLBSB1-MB42	16	5.60	6.70	8.30	7.40	8.00
BTB0.830-18PLBSB1-MB42	18	6.40	7.50	9.10	8.20	
BTB0.830-20PLBSB1-MB42	20	7.20	8.30	9.90	9.00	
BTB0.830-22PLBSB1-MB42	22	8.00	9.10	10.70	9.80	
BTB0.830-24PLBSB1-MB42	24	8.80	9.90	11.50	10.60	12.00
BTB0.830-26PLBSB1-MB42	26	9.60	10.70	12.30	11.40	
BTB0.830-28PLBSB1-MB42	28	10.40	11.50	13.10	12.20	
BTB0.830-30PLBSB1-MB42	30	11.20	12.30	13.90	13.00	
BTB0.830-32PLBSB1-MB42	32	12.00	13.10	14.70	13.80	16.00
BTB0.830-34PLBSB1-MB42	34	12.80	13.90	15.50	14.60	
BTB0.830-36PLBSB1-MB42	36	13.6	14.70	16.30	15.40	
BTB0.830-38PLBSB1-MB42	38	14.40	15.50	17.10	16.20	
BTB0.830-40PLBSB1-MB42	40	15.20	16.30	17.90	17.00	20.00
BTB0.830-44PLBSB1-MB42	44	16.80	17.90	19.50	18.60	
BTB0.830-50PLBSB1-MB42	50	19.20	20.30	21.90	21.00	
BTB0.830-60PLBSB1-MB42	60	23.20	24.30	25.90	25.00	
BTB0.830-70PLBSB1-MB42	70	27.20	28.30	29.90	29.00	24.00
BTB0.830-80PLBSB1-MB42	80	31.20	32.30	33.90	33.00	
BTB0.830-100PLBSB1-MB42	100	39.20	40.30	41.90	41.00	

序号	品名	材质
①	0.8 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0, 颜色:黑色

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE:0.8 Pitch双槽立式BTB母座 业务图(单高3.0)	
DECIMALS: X.:±0.50 X.X:±0.20 X.XX:±0.10		PAR BTB0.830-XPLBSB1-MB42 DWN Lucas CHKD Ethan APVD Jacob SCALE:1:1 UNIT:MM SIZE:A4 SHEET:1F1 REV:A	
CUSTOMER COPY			