






RoHS



RECOMMENDED PCB LAYOUT (T:1.60mm)
TOLERANCE UNSPECIFIED ±0.10mm

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02

备注:**1) 材质:**

- 1-1 本体: LCP 94V-0 黑色
1-2 端子: 青铜 T=0.20mm
1-3 铜壳: 青铜 T=0.50mm

2) 镀层:

- 2-1 端子: 所有面镀镍, 接点镀金G/F, 焊脚镀锡100u",

3) 技术规格


- 3-1. 额定电压: 40V
3-2. 额定电流: 0.5A
3-3. 绝缘电阻: 100兆欧最小
3-4. 接触电阻: 30毫欧最大
3-5. 操作温度: -20度到85度
3-6. 插入力: 44.1N Max
3-7. 拔出力: 9.8~44.1N;
3-8. 耐久: 10000次

MATERIAL LIST:

3	SHELL	1	C2680	PLATED NI
2	HOUSING	1	LCP	UL94V-0,BL
1	CONTACT	19	C2680R-H	PLATED Au
NO.	ITEM	Q'TY	DESCRIPTION	FINISH


MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic TechnologyCo.,Ltd			
X.* ±2"	X.* ±2"				
X ±0.30	.X ±0.012				
XX ±0.20	.XX ±0.008				
XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd		TITLE	HDMI 19P AF 板上型SMT 铜壳带耳 11.38螺丝孔 四脚插板	DR	
		PART NO.	105011112	CHKD	
		PRO J.	PAGE 1/2 UNITS mm	APPD	
		SIZE	A4 SCALE 1:1 DIS NO.		

RoHS



NOTES

1. NUMBER OF CONNECTORS: 250PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 2000PCS/CARTON


COVER TAPE PEELING ANGLE: 165°~180°

PEELING FORCE: 20~130g

CARRIER TAPE


USER DIRECTION OF UNREELING

DETAIL B




8-REEL

4-TRIANGLE PARTITION



TAPE ON

LABEL

CARTON
342*342*250

MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DongGuan JinBiLai Metal Plastic Technology Co., Ltd			
X.* ±2"	X.* ±2"		HDMI 19P AF 板上型SMT 铜壳带耳 11.38螺丝孔 四脚插板		
X ±0.30	.X ±0.012				
XX ±0.20	.XX ±0.008				
XXX ±0.10	.XXX ±0.004				
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd. COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co., Ltd.		TITLE		DR	
		PART NO.		CHKD	
		PRO J.	PAGE 2/2	UNITS mm	APPD
		SIZE	A4	SCALE 1:1	DIS NO.