









DETAIL A
CIRCUIT NUMBERING
AND LIGHTPIPE IDENTIFICATION



RECOMMENDED PCB LAYOUT - COMPONENT SIDE
RECOMMENDED PCB THICKNESS : 2.36MM(.093 INCH)
(MINIMUM PCB THICKNESS : 1.57)

THE ENTIRE AREA OF THE CONNECTOR FOOTPRINT
TO BE CONSIDERED THE KEEP OUT AREA FOR COMPONENTS
THIS AREA IS INDICATED BY THE DASHED LINE

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP 754515001 2X6YD-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:2/4
			.XXX±0.10		REV:A




OUTER LIGHTPIPE
OUTLINE-TYP

Technical drawing of a circuit board layout showing dimensions and component placement. The drawing includes the following details:

- Dimensions:**
 - Overall width: 11.00
 - Overall height: 8.75
 - Distance between vertical centerlines: 7.20
 - Distance between horizontal centerlines: 7.50
 - Distance from left edge to first vertical centerline: 1.90
 - Distance from right edge to first vertical centerline: 1.90
 - Distance from top edge to first horizontal centerline: 1.25 TYP.
 - Distance from bottom edge to first horizontal centerline: 0.80 TYP.
 - Distance between horizontal centerlines of the two modules: 3.60
- Components and Features:**
 - CIRCUIT #1 TOP MODULE:** Indicated by a crosshair symbol (+) in the top-left corner.
 - CIRCUIT #1 BOTTOM MODULE:** Indicated by a crosshair symbol (+) in the bottom-right corner.
 - Ø1.85±0.05 2 PLACES:** Dimension for the diameter of the two circular holes in the top module.
 - Ø0.60±0.05 TYP:** Dimension for the diameter of the typical circular holes in the bottom module.
 - ØØ.10Ⓜ A/B:** Dimension for the diameter of the typical circular holes in the bottom module.
- Section Lines:** Indicated by -A- and -B- symbols.

TERMINAL TAIL PATTERN

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd					
PART NO. SFP 754515001 2X6YD-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4	
APPROVE	CHECK	DRAW	.X±0.20	.X±1°		SCALE: 1:1	SHEET:3/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°				
			.XXX±0.10					



BEZEL CUT-OUT CENTER SPACING DETAIL

SECTION Z-Z

TITLE SFP 2X6 CAGE+CONNECTOR			深圳磁联达电子有限公司 CND-tek Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP 754515001 2X6YD-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:4/4	REV:A
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°			
			.XXX±0.10				